


REV.	DATE	DESCRIPTION
NC	01/02/07	INITIAL RELEASE



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS		DATE		Amphenol Connex				
7						DRAWN	G.R.S.	01/02/07						
6						CHECKED				PART DESCRIPTION 1.0/2.3 PCB BULKHEAD RECEPTACLE – 75ohm				
5						ISSUED								
4	SPANNER NUT	BRASS	NICKEL	1		SHEET	1	OF	1	PART NO. 282121–75				
3	CONTACT PIN	BER. COPPER	GOLD	1	CAD FILE				DWG. NO. 282121–75.DWG					
2	INSULATOR	TEFLON	NATURAL	1	C:/282/282121–75.DWG									REV. A
1	BODY	BRASS	GOLD	1	DO NOT SCALE DRAWING									
DESCRIPTION MATERIAL FINISH QTY														