


REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	SEP 25/17	L.CHAN




FRONT VIEW



SIDE VIEW





RECOMMENDED P.C.B. LAYOUT

(COMPONENT SIDE OF BOARD)




1. MATERIALS:

CONTACTS: PHOSPHOR BRONZE,
PLATING: SELECTIVE GOLD PLATING ON MATING SURFACES. SEE PART NO. FOR THICKNESS.
50 MICRO" MIN. NICKEL OVERALL.
100 MICRO" MIN. MATTE TIN OR GOLD FLASH ON TAILS.

HOUSING: ENGINEERING PLASTIC
COLOR – BLACK.
FLAMMABILITY RATING UL 94V–0

SHIELD: COPPER ALLOY

PLATING: NICKEL WITH TIN DIPPED PCB TAILS.



RECOMMENDED PANEL CUTOUT

AMPHENOL PART NO.: RJSBE–X380–C1

GOLD PLATING OPTION:
D = 6u'' GOLD PLATING
G = 15u'' GOLD PLATING
J = 30u'' GOLD PLATING
5 = 50u'' GOLD PLATING

UNLESS SPECIFIED OTHERWISE	DRAWN RONNIE.C	SEP 25/17	Amphenol Canada Corp. www.amphenolcanada.com
PRIMARY UNITS INCHES	CHECKED AMY.Z	SEP 25/17	
SECONDARY MILLIMETERS	M.E. APP'D		TITLE: MODULAR JACK, 8 CONTACTS, WITHOUT LEDS SHIELDED, .050'' CONTACT TAIL SPACING, WITH GOLD PLATING OPTION– RoHS COMPLIANT
REFERENCE IN PARENTHESES	Q.A. APP'D		
	DWG APP'D		
1 DECIMAL PLACE	ENG. REL. NO.		
2 DECIMAL PLACES	REF. EAR# RJ17172		DWG NO. P–RJSBE–X380–C1 REV A
3 DECIMAL PLACES ±0.015	THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING	
ANGULAR DEGREES ±1.5°			CODE ID NO. 03554 DWG SIZE SCALE SHEET 1 OF 1

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

Downloaded from Arrow.com.