




Color: ■ black metallic

The configurable 852-1305/000-001 Industrial ETHERNET Switch is equipped with eight 10/100/1000BASE-T ports and four 1000BASE-SX/LX SFP ports (SFP modules are available as an option).
Packaged in a rugged housing, this switch offers both a redundant power supply and relay-based function monitoring. These functions, along with extensive ETHERNET switch options, make it ideal for a wide range of applications.

Features:

- Web-based/SNMP management
- Redundant DC power supply
- Power supply range: 12 ... 48 VDC
- Diagnostics via Modbus® and SNMP
- DIP switches to set alarm functions
- Autonegotiation at all 10/100/1000Base-T ports
- Auto-MDI/MDIX (crossover) at all 10/100/1000Base-T ports
- IGMP snooping for multicast filtering
- Port configuration, status, statistics
- Port trunking
- SNMP v1/v2c and RMON
- Approval (IEC 61850-3) for the energy market
- Firmware update and switch configuration via USB storage medium

Technical data	
Switching mode	Store-and-forward; non-blocking
Number of 1 Gb/s ports	8
Number of 1 Gb/s ports SFP	4
Communication standards	IEEE 802.3 10BASE-T IEEE 802.3u 100BASE-TX IEEE 802.3ab 1000BASE-T IEEE 802.3z 1000BASE-SX/LX IEEE 802.3x Flow Control IEEE 802.1d Spanning Tree Protocol (STP) IEEE 802.1w Rapid Spanning Tree Protocol (RSTP) IEEE 802.1s Multiple Spanning Tree Protocol (MSTP) IEEE 802.1Q VLAN Tagging IEEE 802.1p Prioritization IEEE 802.1X Port Authentication IEEE 802.1ab Link Layer Discovery Protocol (LLDP) IEEE 802.3ad Link Aggregation ITU-T G8032v1/v2 Ethernet Ring Protection Switching (ERPS)
Redundancy function	Redundant DC power supply; STP; RSTP; MSTP; Jet Ring < 300 ms; Xpress Ring < 20 ms; Dual Homing < 20 ms; Dual Ring; ERPSv2 < 50 ms; LACP



Technical data	
Configuration options	DIP switch for signal contact Web-Based Management Command Line Interface SNMPv1/v2c/v3 USB storage medium
Diagnostics	Signal contact; Modbus TCP; Port status; Port statistics; Port load; Traffic monitor; SFP information; Syslog; Mail alarm; SNMP traps; Loop detection; ... Alarm contact; Alarm relay; NO; 1 A at 24 VDC
MAC table (size)	16000 addresses
Jumbo frame size	10000 bytes
Supply voltage	12 ... 48 VDC; 24 VDC (DNV GL); 24, 48 VDC (LR)
Power consumption (max.)	18 W
Current consumption (max.)	1500 mA
ESD (contact/air discharge)	8 KV / 15 KV
Transmission rate	Copper cable: 10/1000 Mbit/s; Fiber optic:1000 Mbit/s
Transmission medium (communication/fieldbus)	Copper cable: Cat. 5e or higher, 100 m maximum cable length; Fiber optic: SX Multi-Mode, LX Single-Mode
Optical fiber type	Single-mode and multi-mode
VLAN	Port-based and tag-based (4k VIDs)
Control Elements	2 x DIP switches: alarm function for supply voltages
Indicators	Device: LED (PWR, RPS, POST) green: power supply (primary), redundant power supply (secondary), POST function; LED (ALM) red: Alarm; LED (SFP) green, Status fiber optic ports; per port: LED (100, LNK/ACT) green: Status 100 Mbps, LNK/ACT ports 1 ... 8

Connection Data	
Connection technology: communication/fieldbus	Copper cable: 8 x RJ-45; Fiber optic: 4 x SFP slots (e.g., with SFP module and LC fiber-optic connector)
Connection technology: supply	1 x Built-in male connector: 231-436/001-000; included female connector (MCS Connectors): 2231-106/026-000
Connection technology: device configuration	1 x RS-232 serial interface

Physical data	
Width	50 mm / 1.969 inches
Height	162 mm / 6.378 inches
Depth	120 mm / 4.724 inches

Mechanical data	
Mounting type	DIN-35 rail

Material data	
Color	black metallic
Housing material	Aluminum
Fire load	0.2 MJ
Weight	855 g
Conformity marking	CE

Environmental requirements		
Ambient temperature (operation)		-40 ... +70 °C (-40 ... +70 °C (CE); -25 ... +70 °C (DNV GL); +5 ... +70 °C (LR))
Ambient temperature (storage)		-40 ... +80 °C
Protection type		IP30
Note on protection type		Use per UL 61010: Indoor
Pollution degree		2 per UL 61010
Relative humidity (without condensation)		95 %
Vibration resistance		Per IEC 60068-2-6
Shock resistance		per IEC 60068-2-27
EMC immunity to interference		per EN 61000-6-2
EMC emission of interference		per EN 61000-6-4

Data Act		
Pre-contractual Information		Data-Act-AUT-Products-Switches

Commercial data		
PU (SPU)		1 pcs
Packaging type		Box
Country of origin		TW
GTIN		4055143898133
Customs tariff number		85176200000

Product Classification		
UNSPSC		43222612
ETIM 9.0		EC000734
ETIM 10.0		EC000734
ECCN		5A992.C

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption

Approvals / Certificates			
General approvals		Declarations of conformity and manufacturer's declarations	
			
Approval	Standard	Certificate Name	
EAC GZO Almaty Standart	TP TC 020/2011	EAC CoC 03083	
IEC Interocean EMC Technology Corp.	IEC 61850-3	18A092117E_C	
KC National Radio Research Agency	Article 58-2, Clause 3	MSIP-REM-W43-ISW852	
		Approval	Standard
		EU-Declaration of Conformity WAGO GmbH & Co. KG	-
			Certificate Name
			-



Approvals for marine applications



Approval	Standard	Certificate Name
DNV DNV GL SE	-	TAA00002YN
LR Lloyds Register	-	LR2631713TA

Downloads

Environmental Product Compliance

Compliance Search
Environmental Product Compliance 852-1305/000-001



Documentation

Manual
Product Manual 8 Port 1000BASE-T + 4-Slot 1000BASE SX-LX Industrial Managed Switch
V 1.0.1 11.07.2023
pdf 15431.62 KB
↓
Function Manual Industrial-Managed-Switches
V 1.0.0 07.07.2026
pdf 5566.70 KB
↓

System Description
Industrial Switches – General Product Information
pdf 1873.93 KB
↓

Bid Text
852-1305/000-001
22.05.2019
docx 17.39 KB
↓
852-1305/000-001
22.05.2019
xml 7.38 KB
↓
ausschreiben.de 852-1305/000-001
↓

CAD/CAE-Data

CAD data
2D/3D Models 852-1305/000-001
↓

CAE data
EPLAN Data Portal 852-1305/000-001
↓
ZUKEN Portal 852-1305/000-001
↓



Runtime Software

Firmware			
0852-1305/0000-0001, Industrial-Managed-Switch	V 14 04.03.2024	zip 16486.67 KB	

1 Compatible Products

1.1 Optional Accessories

1.1.1 Cables and connectors

1.1.1.1 Connector plug



Item No.: 750-979/000-011
Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568A; AWG 22; Strain relief



Item No.: 750-979/000-021
Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568A; AWG 24; Strain relief



Item No.: 750-979/000-012
Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568B; AWG 22; Strain relief



Item No.: 750-979/000-022
Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568B; AWG 24; Strain relief



Item No.: 750-977/000-011
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 22



Item No.: 750-978/000-011
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 22; Strain relief



Item No.: 750-977/000-021
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 24



Item No.: 750-978/000-021
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 24; Strain relief



Item No.: 750-977/000-012
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 22



Item No.: 750-978/000-012
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 22; Strain relief



Item No.: 750-977/000-022
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 24



Item No.: 750-978/000-022
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 24; Strain relief



Item No.: 750-979/000-013
Connector PROFINET; RJ-45; Cat. 6A; angled; AWG 22; Strain relief



Item No.: 750-977/000-013
Connector PROFINET; RJ-45; Cat. 6A; straight; AWG 22



Item No.: 750-978/000-013
Connector PROFINET; RJ-45; Cat. 6A; straight; AWG 22; Strain relief



Item No.: 750-975
ETHERNET RJ-45 connector, IP20; ETHERNET 10/100 Mbit/s; for field assembly



Item No.: 750-976
PROFINET RJ-45 connector, IP20; ETHERNET 10/100 Mbit/s; for field assembly

1.1.2 Interface module

1.1.2.1 Interface module



Item No.: 289-195
Interface module; RJ-45; IDC technology; Cat. 6; in mounting carrier; with shield connection



Item No.: 289-175
Interface module; RJ-45; PCB terminal blocks, double-row; Cat. 5; in mounting carrier; with shield connection; with shield clamping saddle; 1,50 mm²



Item No.: 289-172
Interface module; RJ-45; RJ-45; Cat. 5; in mounting carrier



Item No.: 289-196
Interface module; RJ-45; with power jumper contacts; PCB terminal blocks; Cat. 5



1.1.3 Plug

1.1.3.1 SFP module



Item No.: 852-1210
SFP Module 1000BASE; LX Single-Mode 1310 nm LC; 10 km; Extended temperature range; Digital Diagnostics Monitoring; silver-colored



Item No.: 852-1200
SFP Module 1000BASE; SX Multi-Mode 850 nm LC; 0.55 km; Extended temperature range; Digital Diagnostics Monitoring; silver-colored



Item No.: 852-1280
SFP Module 1000BASE; ZX Single-Mode 1550 nm LC; 80 km; Extended temperature range; Digital Diagnostics Monitoring; silver-colored

1.1.4 Power supply

1.1.4.1 Power Supply



Item No.: 787-1602
Switched-mode power supply; Classic; 1-phase; 24 VDC output voltage; 1 A output current; NEC Class 2; DC OK signal



Item No.: 787-1632
Switched-mode power supply; Classic; 1-phase; 24 VDC output voltage; 10 A output current; TopBoost; DC OK contact



Item No.: 787-1606
Switched-mode power supply; Classic; 1-phase; 24 VDC output voltage; 2 A output current; NEC Class 2; DC OK signal



Item No.: 787-1622
Switched-mode power supply; Classic; 1-phase; 24 VDC output voltage; 5 A output current; TopBoost; DC OK contact



Item No.: 787-1635
Switched-mode power supply; Classic; 1-phase; 48 VDC output voltage; 10 A output current; TopBoost; DC OK contact



Item No.: 787-1623
Switched-mode power supply; Classic; 1-phase; 48 VDC output voltage; 2 A output current; DC OK signal



Item No.: 787-1633
Switched-mode power supply; Classic; 1-phase; 48 VDC output voltage; 5 A output current; TopBoost; DC OK contact

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com