




OGA DIAGONAL: 16.46 [418.06]
VA DIAGONAL: 15.74 [399.76]
PA DIAGONAL: 14.85 [377.12]







(SER)
EXII-7720SC
98-0003-2217-6
SERIAL CONTROLLER
SOLDER SIDE



(USB R)
EXII-7760UC
98-0003-2814-0
USB CONTROLLER
SOLDER SIDE



(FFC)



TOP LEVEL NUMBER	US NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
17-8201-203	98-0003-2559-1	FFC	4.27" [108.46]	AG500	23655
17-8201-221	98-0003-2563-3	SER	4.27" [108.46]	AG500	23655
17-8201-206	98-0003-2560-9	NOV	SEE DWG	AG500	23655
17-8201-204	98-0003-2937-9	FFC	6.00" [152.40]	AG500	23655
17-8201-223	98-0003-2564-1	SER	6.00" [152.40]	AG500	23655
17-8201-218	98-0003-2938-7	USB R	4.27" [108.46]	AG500	23655
17-8201-205	98-0003-3242-3	FFC	8.00" [203.20]	AG500	23655
17-8201-226	98-0003-3243-1	USB R	8.00" [203.20]	AG500	23655
17-8201-227	98-0003-3244-9	SER	8.00" [203.20]	AG500	23655


NOTES:

- WEIGHT OF GLASS IN GRAMS: 643±10%
- NICOMATIC HOUSING P/N: OLOS
NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
HOUSING ORIENTED WITH LATCH DOWN

PINOUT	
1	LR
2	LL
3	SHLD
4	UL
5	UR

UNITS INCHES [MM]

TOLERANCES UNLESS OTHERWISE SPECIFIED
.X ± .03 [.76]
.XX ± .015 [.38]
ANGLES ± 1°



DO NOT SCALE DRAWING

SCALE 1 = 1



3M TOUCH SYSTEMS
METHUEN, MA
USA
© COPYRIGHT 2004
THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE
3M COMPANY AND MAY NOT BE REPRODUCED
WITHOUT 3M WRITTEN PERMISSION OR USED OR
DISCLOSED FOR OTHER THAN 3M AUTHORIZED
PURPOSES.

DRAWN K.CROWLEY 9/05

H	REVISED PER CO 036256	4/13	SB
G	REVISED PER CO 033533	10/11	SB
F	REVISED PER CO 033535	9/11	SB
REV	CHANGE NOTICE	DATE	DRW

TITLE	MARKETING DRAWING SCT32NN 15.74"
CAD FORMAT	AUTOCAD
SHEET	1 OF 1
SIZE	C
DOCUMENT NO.	28295-MKT
REV	H