



+ CONNECTORS
HOUSINGS



✓ Active

TE CONNECTIVITY (TE)
MOD 4 REC.HSG 1X10P
[AMPMODU](#) | [AMPMODU IV/V](#)

1-925370-0
TE Internal Number: 1-925370-0

[EU RoHS Compliant](#)
[EU ELV Compliant](#)

Number of Positions 20
Centerline (Pitch) 2.54 mm [.1 in]
Termination Method to Wire/Cable Crimp
Number of Rows 2
Row-to-Row Spacing 2.54 mm [.1 in]

[↓](#) **PRODUCT DRAWING**
English

[↓](#) **3D PDF**

DOCUMENTATION

Product Drawings

AMPMODU IV GEHAEUSE, EINREIHIG Housing, Single Row
PDF
English

CAD Files

Customer View Model
2D_DXF.ZIP
English

3D PDF
PDF
3D

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Product Specification

AMPMODU Mod 1/2 Wire To Board Standard Pressure Contact Interconnection System

PDF

English

Agency Approvals

Agency Approval Document

AMPMODU CONNECTOR REPORT (GERMANY)

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- Row-to-Row Spacing 2.54 mm [.1 in]
- Connector & Contact Terminates To Printed Circuit Board
- Glow Wire Rating Standard Part - Not Glow Wire
- Strain Relief With
- Connector Type Housing
- Connector Style Receptacle
- Product Type Connector

Configuration Features

- Number of Positions 20
- Number of Rows 2

Electrical Characteristics

- Operating Voltage 250 VAC

Body Features

- Color Green

Contact Features

- Contact Type Socket

Termination Features

Termination Method to Wire/Cable Crimp

Mechanical Attachment

Mating Connector Lock Without

Mating Retention With

Mating Retention Type Lock

Mating Alignment Without

Mating Alignment Type Polarization

Housing Features

Centerline (Pitch) 2.54 mm [.1 in]

Housing Configuration Both Ends Closed

Housing Material Polyamide 6.6 GF

Housing Color Green

Dimensions

Length (in) 4.99

Height (in) .21

Usage Conditions

Operating Temperature Range (°C) -65 – 105

Operation/Application

For Use With AMPMODU Mod II .025 inch Headers

Industry Standards

UL Flammability Rating UL 94V-0

Packaging Features

Packaging Quantity 25

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF