



MICRO USB 2.0 Series 801 Mighty Mouse




801-084 and 801-085 Receptacle with USB Micro "AB" Female Interface to Crimp Removable Contacts



Receptacles
and Rear View of
Crimp Termination

How To Order				
Sample Part Number	801-084	-02 MUSB	-M	A
Series	801-084 = Shield Termination Porch 801-085 = Accessory Threads			
Shell Style ¹	02 = Square Flange Mount Receptacle 07 = Jam Nut Mount Receptacle			
Shell Material and Finish ¹	NF = AL/Cadmium, Olive Drab M = AL/Electroless Nickel MT = AL/Nickel PTFE ZNU = AL/Black Zinc Nickel			
Alternate Key Positions ¹	A, B, C, D, E, F			


801-084-02 AND 801-085-02 SQUARE FLANGE



801-084-02 Receptacle
with Shield Termination Porch

801-085-02 Receptacle
with Accessory Threads

801-085-07 AND 801-085-07 JAM NUT



801-084-07 Receptacle
with Shield Termination Porch

801-085-07 Receptacle
with Accessory Threads

NOTES

- See Section A for recommended panel, additional finishes and alternate keyway positions.
- Receptacle connectors mate with Glenair plugs 801-082, 801-083, 801-087 and 801-088
- Contacts are crimp type, and used in rear release retention system (809-001)

Wire Schematic				
Rear Grommet Side			Mating Side	
Label	Cable Color (Typ)		ID	Micro USB Pin Description
V	Red		1	VBUS (V)
G	Black		2	D-
D-	White		3	D+
D+	Green		4	ID
ID	None		5	GND (G)
				⏏ Ground