

Part Number : [190670007](#)


Product Description : NylaKrimp Funnel Entry Ring
Tongue Terminal for 8 AWG Wire, Stud Size 10 (M5)

Series Number : 19067

Status : Active

Product Category : Ring and Spade Terminals

Engineering Part Number : D-950-10T



Documents and Resources

Drawings

[190670007_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[PS-19902-015-001.pdf](#)

[PS-19902-016-001.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)4165-DC (25 June 2025) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|--------------|---|
| Status | Active |
| Category | Ring and Spade Terminals |
| Series | 19067 |
| Description | NylaKrimp Funnel Entry Ring Tongue Terminal for 8 AWG Wire, Stud Size 10 (M5) |
| Keyword | Ring Terminal, Ring Terminals |
| Product Name | NylaKrimp |
| Style | Ring |
| Type | Ring Terminal |
| UPC | 800753065291 |

Agency

| | |
|-----|---------|
| CSA | LR18689 |
| UL | E32244 |

Physical

| | |
|---------------------------|-----------------|
| Barrel Type | Closed - Brazed |
| Flammability | 94V-2 |
| Insulation | Nylon (PA) |
| Material - Plating Mating | Tin |
| Net Weight | 3.723/g |

| | |
|-----------------------------|-----------------------|
| Packaging Type | Adhesive Tape on Reel |
| Plating min - Mating | 2.540µm |
| Plating min - Termination | 2.540µm |
| Stud Size | 10 (M5) |
| Termination Interface Style | Crimp or Compression |
| Wire Insulation Diameter | 8.98mm max. |
| Wire Size (AWG) | 8 |

Solder Process Data

| | |
|------------------------------|-----|
| Lead-Free Process Capability | N/A |
|------------------------------|-----|

Application Tooling

Global

| Description | Part Number |
|--|------------------|
| ATP Style Crimp Press that Requires Perishable Tooling Kits to Process Product on Tape | <u>190470001</u> |
| Crimp Dies for 8 AWG Insulkrimp and NylaKrimp Mylar Tape, use with Tape Crimp Module and TM-4000 Crimp Press | <u>190472030</u> |
| ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press | <u>192880220</u> |

This document was generated on May 09, 2026