

## VLS3010ET-4R7M

## Production (NRND)

**Product Status** Recommended Alternate Part No. : [VLS3010CX-4R7M-1](#) (Interchangeability is not guaranteed.)

**Applications** Commercial Grade

Wire Wound

Feature Shield

Magnetic Shield

Ferrite Core

Ferrite Core

**Series | Type** VLS-E

**Brand** TDK

**Environmental**



RoHS



REACH



Halogen Free



Lead Free



## Size

Length(L)	3.00mm $\pm 0.10$ mm
Width(W)	3.00mm $\pm 0.10$ mm
Thickness   Height	1.00mm Max.
Recommended Land Pattern (A)	1.00mm Nom.
Recommended Land Pattern (B)	1.00mm Nom.
Recommended Land Pattern (C)	3.00mm Nom.

## Electrical Characteristics

Inductance	4.7 $\mu$ H $\pm 20\%$ at 1MHz
Rated Current (L Change) [Typ.]	900mA (30% Down)
Rated Current (L Change) [Max.]	810mA (30% Down)
Rated Current (Temperature Rise) [Typ.]	1.3A (40°C Rise)
Rated Current (Temperature Rise) [Max.]	
DC Resistance [Typ.]	170m $\Omega$
DC Resistance [Max.]	204m $\Omega$
Rated Voltage [Max.]	
Self Resonant Frequency [Min.]	
Self Resonant Frequency [Typ.]	
Q [Min.]	
Q [Typ.]	

## Other

Operating Temp. Range	-40 to 105°C (Including Self-Temp. Rise)
Soldering Method	Reflow
AEC-Q200	NO
Packing	Embossed (Plastic)Taping [180mm Reel]

! Images are for reference only and show exemplary products.

! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.







## VLS3010ET-4R7M

Package Quantity	2000pcs
Weight	0.036g

! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.

## VLS3010ET-4R7M

## Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)




! Images are for reference only and show exemplary products.

! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

VLS3010ET-4R7M



## Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)



! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.

VLS3010ET-4R7M

## Associated Images



! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.