



General Description

The EN5520 is part of Maxlinear's second generation low power CMOS digital Channel Stacking Switch (dCSS) product family for MDU switch applications. The EN5520 enables aggregating up to 8.4 GHz of satellite content from four wideband RF inputs to single or dual L-band IF outputs.

The device integrates a 32-channel stacking engine that is controlled by an embedded microcontroller. The 32 configurable Channel Select Filters (CSFs) can be allocated to any of the two IF outputs to offer complete flexibility to the operators for distributing multi-channel content over coaxial cable to a single family home or to two Multiple Dwelling Units (MDUs) at the lowest system cost.

Each IF output is configurable in channel stacking mode or in legacy L-band bypass mode, and features a dedicated DiSEqC2.x compatible modem for remote control by the subscriber STBs.


Applications

- Digital channel stacking multi-switches

Features

- Four wideband RF inputs with bandwidth from 250 MHz to 2350 MHz
- Two L-band IF outputs with bandwidth from 950 MHz to 2150 MHz
 - CSS or legacy L-band bypass modes
 - Positive/negative IF tilt correction
- Configurable 32-channel stacking engine
 - Programmable channel select filters
 - Fully flexible user bands allocation
 - Spectral inversion
- Integrated microcontroller and control APIs for customer application software
 - DiSEqC 2.x compatible modems with support for *EN50494* and *EN50607* standards
 - I²C interface
 - Multiple GPIO pins
 - SPI flash interface
 - UART debug port
- Single external 25 MHz reference crystal
- Low power consumption
- Small 9 x 9 mm² QFN, 76-pin package

Block Diagram



Ordering Information

Ordering Part Number	Description
EN5520-01-1	9 mm x 9 mm² QFN Package RoHS Green Compliant



MaxLinear, Inc.

5966 La Place Court, Suite 100

Carlsbad, CA 92008

760.692.0711 p.

760.444.8598 f.

www.maxlinear.com

The content of this document is furnished for informational use only, is subject to change without notice, and should not be construed as a commitment by MaxLinear, Inc. MaxLinear, Inc. assumes no responsibility or liability for any errors or inaccuracies that may appear in the informational content contained in this guide. Complying with all applicable copyright laws is the responsibility of the user. Without limiting the rights under copyright, no part of this document may be reproduced into, stored in, or introduced into a retrieval system, or transmitted in any form or by any means (electronic, mechanical, photocopying, recording, or otherwise), or for any purpose, without the express written permission of MaxLinear, Inc.

Maxlinear, Inc. does not recommend the use of any of its products in life support applications where the failure or malfunction of the product can reasonably be expected to cause failure of the life support system or to significantly affect its safety or effectiveness. Products are not authorized for use in such applications unless MaxLinear, Inc. receives, in writing, assurances to its satisfaction that: (a) the risk of injury or damage has been minimized; (b) the user assumes all such risks; (c) potential liability of MaxLinear, Inc. is adequately protected under the circumstances.

MaxLinear, Inc. may have patents, patent applications, trademarks, copyrights, or other intellectual property rights covering subject matter in this document. Except as expressly provided in any written license agreement from MaxLinear, Inc., the furnishing of this document does not give you any license to these patents, trademarks, copyrights, or other intellectual property.

MaxLinear, the MaxLinear logo, and any MaxLinear trademarks, MxL, Full-Spectrum Capture, FSC, G.now, AirPHY and the MaxLinear logo are all on the products sold, are all trademarks of MaxLinear, Inc. or one of MaxLinear's subsidiaries in the U.S.A. and other countries. All rights reserved. Other company trademarks and product names appearing herein are the property of their respective owners.

© 2019 MaxLinear, Inc. All rights reserved.