Pushing Performance
Since 1945

M23 12 Male-C CCW



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 112 3011
Specification	M23 12 Male-C CCW
HARTING eCatalogue	https://harting.com/09151123011

Identification

Category	Inserts
Series	Circular connectors M23
Identification	Signal
Element	Inserts
Specification	Marking in opposite direction

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	12
Details	Please order crimp contacts separately. 12x 1 mm

Technical characteristics

Conductor cross-section (mm²)	0.08 ... 1.5 mm²
Rated current	8 A
Rated voltage	200 V
Rated impulse voltage	2.5 kV
Pollution degree	3
Insulation resistance	$>10^{10}$ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	White
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076

Commercial data

Packaging size	5
Net weight	2.76 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140187092
eCl@ss	27440223 Contact insert for circular connectors
ETIM	EC003557
UNSPSC 24.0	39121421

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.