

TINA2-RS

~14° spot beam optimized for Nichia NS6x83.
Assembly with holder and installation tape.



SPECIFICATION:


Dimensions	Ø 16.1
Height	11 mm
Fastening	tape
ROHS compliant	yes 

MATERIALS:

Component	Type	Material	Colour	Finish	Length (mm)
TINA2-RS	Single lens	PMMA	clear		
TINA2-HLD-N83-BLK	Holder	PC	black		
TINA-TAPE3	Tape	Acryl tape	black		

ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
CA11171_TINA2-RS » Box size: 451 x 241 x 298 mm	4140	230	230	8.4




See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):




LED MX-6
FWHM / FWTM 18.0° / 40.0°
Efficiency 89 %
Peak intensity 5.2 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED LUXEON V
FWHM / FWTM 21.0° / 41.0°
Efficiency 82 %
Peak intensity 4.3 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files




LED NS3x83
FWHM / FWTM 15.0°
Efficiency 93 %
LEDs/each optic 1
Light colour/type White
Required components:

Light distribution files

OPTICAL RESULTS (MEASURED):





LED NS6x83
FWHM / FWTM 19.0° / 42.0°
Efficiency 93 %
Peak intensity 5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED LH508A
FWHM / FWTM 26.0° / 53.0°
Efficiency 76 %
Peak intensity 2.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED XP-E2
 FWHM / FWTM 12.0° / 22.0°
 Efficiency 91 %
 Peak intensity 18.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED XP-G2
 FWHM / FWTM 14.0° / 27.0°
 Efficiency 91 %
 Peak intensity 12.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED XP-G3
 FWHM / FWTM 16.0° / 34.0°
 Efficiency 87 %
 Peak intensity 7.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED XP-L HI
 FWHM / FWTM 14.0° / 28.0°
 Efficiency 92 %
 Peak intensity 10.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED XP-L2
 FWHM / FWTM 22.0° / 41.0°
 Efficiency 86 %
 Peak intensity 4.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED XT-E
 FWHM / FWTM 14.0° / 26.0°
 Efficiency 85 %
 Peak intensity 11.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED	LUXEON CZ
FWHM / FWTM	12.0° / 22.0°
Efficiency	92 %
Peak intensity	17.7 cd/lm
LEDs/each optic	1
Light colour/type	Red
Required components:	



Light distribution files




LED	LUXEON HL2X
FWHM / FWTM	16.0° / 32.0°
Efficiency	91 %
Peak intensity	8.5 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files



LED	SST-20 Gen1
FWHM / FWTM	12.0° / 24.0°
Efficiency	88 %
Peak intensity	14.5 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED NV4WB35AM
 FWHM / FWTM 22.0° / 40.0°
 Efficiency 89 %
 Peak intensity 4.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED NV4WB35AM
 FWHM / FWTM 22.0° / 40.0°
 Efficiency 89 %
 Peak intensity 4.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED NVSW219F
 FWHM / FWTM 16.0° / 32.0°
 Efficiency 91 %
 Peak intensity 8.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED	NVSW519A
FWHM / FWTM	20.0° / 39.0°
Efficiency	86 %
Peak intensity	5.5 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files



LED	NVSxx19B/NVSxx19C
FWHM / FWTM	16.0° / 31.0°
Efficiency	86 %
Peak intensity	8.2 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	




Light distribution files



Opto Semiconductors

LED	OSLON Square CSSRM2/CSSRM3
FWHM / FWTM	14.0° / 30.0°
Efficiency	90 %
Peak intensity	9.9 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	





Light distribution files

OPTICAL RESULTS (SIMULATED):

OSRAM

Opto Semiconductors

LED SFH 4715AS
FWHM / FWTM 10.0° / 20.0°
Efficiency 89 %
LEDs/each optic 1
Light colour/type IR
Required components:





Light distribution files

OSRAM

Opto Semiconductors

LED SFH 4716AS
FWHM / FWTM 12.0° / 22.0°
Efficiency 88 %
LEDs/each optic 1
Light colour/type IR
Required components:





Light distribution files

OSRAM

Opto Semiconductors

LED SFH 4717AS
FWHM / FWTM 12.0° / 25.0°
Efficiency 85 %
LEDs/each optic 1
Light colour/type IR
Required components:





Light distribution files

OPTICAL RESULTS (SIMULATED):

OSRAM
Opto Semiconductors



LED SFH 4725AS
FWHM / FWTM 10.0° / 20.0°
Efficiency 89 %
LEDs/each optic 1
Light colour/type IR
Required components:



Light distribution files

OSRAM
Opto Semiconductors



LED SFH 4725S
FWHM / FWTM 12.0° / 20.0°
Efficiency 89 %
LEDs/each optic 1
Light colour/type IR
Required components:



Light distribution files

OSRAM
Opto Semiconductors

LED SFH 4727AS
FWHM / FWTM 13.0° / 25.0°
Efficiency 85 %
LEDs/each optic 1
Light colour/type IR
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG


LED LH351B
FWHM / FWTM 16.0° / 32.0°
Efficiency 90 %
Peak intensity 8.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

SAMSUNG

LED LH351C
FWHM / FWTM 18.0° / 33.0°
Efficiency 92 %
Peak intensity 7.8 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy
Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.
228 West Page Street
Suite D
Sycamore IL 60178
USA

**Ledil Optics Technology
(Shenzhen) Co., Ltd.**
405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

**Local sales and technical
support**
www.ledil.com/
where_to_buy

Shipping locations
Poznan, Poland
Hong Kong, China

Distribution Partners
www.ledil.com/
where_to_buy