






REVISION RECORD			
REV	ECN	DESCRIPTION	DRFT DATE




- NOTES1:
- UL Standard
 - 1. Rated voltage/current : 150V / 10A
 - 2. Torque Value : M2 , 1.77Lb.in
 - 3. Wire Range : 26~16AWG

- IEC Standard
- 1. Rated voltage/current : 130V / 10A
 - 2. Torque Value : M2 , 0.2N.m
 - 3. Wire Range : 0.5~1.0mm²

- NOTES2:
- 1. Dimension shall be interpreted per ASME Y14.5-2009
 - 2. Pitch : 3.5/3.81mm, Poles : N=02~24P
 - 3. Stripping length : 4~5mm
 - 4. Withstanding voltage : AC1250V/1Min
 - 5. Operating temperature : -40°C~+105°C
 - 6. Undimensioned tolerances:

Pitch range in mm	Nominal dimension range		mm	mm	mm	mm	mm
	Over	Under					
6 TO 10	10	TO	30	TO	100	150	0.1/10
10 TO 24	24	TO	60	TO	100	150	<
30 TO 60	60	TO	100	TO	150	±2°	
60 TO 100	100	TO	150	TO	1.00	±1.30	
100 TO 150	150	TO	1.00	TO	±1.30		

7. RoHS Compliance



- 1.(Grey)
- 2.(Blue)
- 3.(Black)
- 4.(Green)
- 5.(Orange)
- 6.(Red)
- 7.(Transparent)
- 8.(Yellow)
- 9.(White)

DETACHED LISTS			
PART NO.:	/	NAME:	DEGSON [®] NINGBO DEGSON ELECTRICAL CO., LTD 宁波高松电子有限公司
APPD:	/	CHKD:	/
DRFT:	/	TITLE:	CUSTOMER DRAWING
THIRD ANGLE PROJECTION		DRAWING NO.:	/
		DO NOT SCALE DRAWING	SCALE
			1:1