



Part Number : [782321001](#)
Product Description : GbX I-Trac Vertical
Receptacle, Power Module, 2 Blades, 80 Amps, Lead-
Free
Series Number : 78232
Status : Active
Product Category : Backplane Connectors



Documents & Resources

Drawings

[782321001_sd.pdf](#)
[PK-78232-001-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications

[PS-78231-006-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Backplane Connectors
Series	78232
Description	GbX I-Trac Vertical Receptacle, Power Module, 2 Blades, 80 Amps, Lead-Free
Application	Backplane, Midplane
Component Type	Power Receptacle
Product Name	GbX I-Trac
UPC	822350856553

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	80.0A
Data Rate	12.0 Gbps
Shielded	No
Shield Type	N/A
Voltage - Maximum	250V DC

Physical

Circuits Detail	80 Amps (40/Split Blade)
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	100
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.500/g
Number of Columns	1
Number of Pairs	6
Number of Rows	2
Orientation	Vertical
Packaging Type	Tray
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
PC Tail Length	2.41mm
Pitch - Mating Interface	2.00mm, 7.40mm
Pitch - Termination Interface	2.00mm, 7.40mm
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-20° to +85°C
Termination Interface Style	Through Hole - Compliant Pin

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
GbX I-Trac Right-Angle Headers	<u>78234</u>

Use with Part(s)

Description	Part Number
GbX I-Trac Vertical Header Modules	<u>75705</u>

Application Tooling

Global

Description	Part Number
Support Tool for Vertical Power Module for 11-Row Receptacle	<u>622018634</u>

This document was generated on Sep 22, 2025