



**Part Number :** [02081003](#)  
**Product Description :** MLX Female Crimp  
Terminal 42024, 20-14 AWG, Reel, Phosphor  
Bronze, Tin (Sn) Plating  
**Series Number :** 42024  
**Status :** Active  
**Product Category :** Crimp Terminals  
**Engineering Number :** 42024-1B1  
**Packaging Alternative :** 02081004 (Bag)




Documents & Resources

**Drawings**  
[002081003\\_sd.pdf](#)

**Specifications**  
[PS-42022-0001-001.pdf](#)  
[TS-42022-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Crimp Terminals
Series	42024
Description	MLX Female Crimp Terminal 42024, 20-14 AWG, Reel, Phosphor Bronze, Tin (Sn) Plating
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	MLX
UPC	800753618411

#### Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.359/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.30mm
Wire Size (AWG)	14, 16, 18, 20
Wire Size mm <sup>2</sup>	N/A

#### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

## Application Tooling

### Global

Description	Part Number
Extraction Tool for MLX 2.13mm Diameter Pin and Socket Crimp Terminals	<u>11010168</u>
PremiumGrade Hand Crimp Tool for MLX Pin and Socket Terminals, 20-14 AWG	<u>638116800</u>
FineAdjust Applicator for Crimp Terminals, 20-14 AWG Wire with 2.08-2.50mm Diameter Insulation	<u>639007500</u>
FineAdjust Applicator for Crimp Terminals, 20-14 AWG Wire with 2.65-3.30mm Diameter Insulation	<u>639009800</u>
FineAdjust Applicator for Crimp Terminals, 20-14 AWG Wire with 2.41-2.95mm Diameter Insulation	<u>639009900</u>
T2 Terminator for MLX Crimp Terminals, 20-14 AWG	<u>639107500</u>
T2 Terminator Tooling Die for Crimp Terminals, 20-14 AWG Wire	<u>639109800</u>
T2 Terminator Tooling Die for Crimp Terminals, 20-14 AWG Wire	<u>639109900</u>

---

This document was generated on Apr 18, 2025