



1Q 2012 Product Selector Guide

Port Processors

Target Applications: HDTVs

Features	SiI9589-3*	SiI9587-3*	SiI9489A	SiI9387A	SiI9381A	SiI9287B	SiI9199
HDMI® Input	5	4	5	5	4	4	3
MHL™ Input	1	1	1	1	1		
HDMI Output	1	1	2	1	1	1	1
InstaPort™	InstaPort™ S	InstaPort™ S	InstaPort™ S	InstaPort™ S	InstaPort™ S	InstaPort™	
ViaPort			•				
Hardware HDCP Repeater			•				
300 MHz TMDS	•	•					
3D Support	•	•	•	•	•	•	•
Audio Return Channel	•	•	•	•	•		
HDMI Ethernet Channel			•	•			
Max HDMI Resolution	4k30p, 1080p120	4k30p, 1080p120	1080p/60Hz, 36 bit (12 bit/color)	1080p/60Hz, 36 bit (12 bit/color)	1080p/60Hz, 36 bit (12 bit/color)	1080p/60Hz, 36 bit (12 bit/color)	1080p/60Hz, 36 bit (12 bit/color)
Max MHL Resolution	1080p/30Hz, 24 bit (8 bit/color)	1080p/30Hz, 24 bit (8 bit/color)	1080p/30Hz, 24 bit (8 bit/color)	1080p/30Hz, 24 bit (8 bit/color)	1080p/30Hz, 24 bit (8 bit/color)		
x.v.Color Support	•	•	•	•	•	•	•
HDCP Decryption, HDCP BIST and Pre-programmed HDCP Keys	•	•	•	•	•	•	
CEC Processor			•	•	•	•	
Advanced Sleep Modes	•	•	•	•	•	•	•
Integrated NVRAM EDID for HDMI and VGA Port	•	•	•	•	•	•	
Package Size	100-pin TQFP	88-pin QFN	128-pin QFP	100-pin QFP	88-pin QFN	72-pin QFN	72-pin QFN
Starter Kit	CP9589-3	CP9587-3	CP9489	CP9387HDMI	CP9381A	CP9287HDMI	CP9199

*Also available in 225 MHz versions

HDMI Receivers

Target Applications: HDTVs

Features	SiI9223A	SiI9127
HDMI® Input	4	2
Display Interface	36-bit	36 bit
Max HDMI Resolution	1080p/60Hz, 36 bit (12 bit/color)	1080p/60Hz, 36 bit (12 bit/color)
RGB, YCbCr Color Space Conversion	•	•
x.v.Color Support	•	•
HDCP Decryption, HDCP BIST and Pre-programmed HDCP Keys	•	•
CEC Processor	•	•
Integrated NVRAM EDID	4	2
Advanced Sleep Modes	•	•
2x I²S and S/PDIF Output	•	•
Slave I²C Interface	•	•
Auto Video/Audio Mode Detection	•	•
Package Size	144-pin TQFP	128-pin TQFP
Starter Kit	CP9223HDMI	CP9127HDMI

iTMDS Transmitters

Target Applications: HDTVs

Features	SiI7172
Input (Single Pixel)	Up to 48-bit
Input (Dual Pixel)	Up to 72-bit
Video Resolution	VGA-UXGA, VGA-QUXGA (Dual)
Deep Color (iTMDS)	Up to 48 bit (16 bit/color)
HDCP Encryption and Pre-programmed HDCP Keys	•
Spread Spectrum Clocking	•
Advanced Sleep Modes	•
24-bit True Color Support in All Modes	•
Package Size	128-pin LQFP
Starter Kit	CP7181-7172, CP7189-7172

iTMDS Receivers

Target Applications: HDTVs

Features	SiI7189	SiI7181	SiI7171
Display Interface	48-bit (1 pixel) 72-bit (2 pixels)	48-bit (1 pixel) 72-bit (2 pixels)	48-bit (1 pixel) 72-bit (2 pixels)
Video Resolution	VGA-UXGA, VGA-QUXGA (Dual)	VGA-UXGA, VGA-QUXGA (Dual)	VGA-UXGA (Single link)
Deep Color (iTMDS)	Up to 48 bit (16 bit/color)	Up to 48 bit (16 bit/color)	Up to 48 bit (16 bit/color)
HDCP Decryption and Pre-programmed HDCP Keys	•		
Advanced Sleep Modes	•	•	•
24-bit True Color Support in All Modes	•	•	•
Package Size	208-pin QFP	208-pin QFP	128-pin LQFP
Starter Kit	CP7189-7172	CP7181-7172	CP7171-7170, CP7171LCD

Port Processors

Target Applications: AVR, HTiB, Soundbar

Features	SiI9575	SiI9573
HDMI® Input	6	6
MHL™ Input	2	2
HDMI Output	2	2
InstaPort™	InstaPort™ S	InstaPort™ S
InstaPrevue	•	•
ViaPort Matrix Switch	•	
Hardware HDCP Repeater	•	•
300 MHz TMDS	•	•
3D Support	•	•
Audio Extraction	•	•
Audio Insertion	•	•
Audio Return Channel	•	•
On-Screen Display	•	•
Max HDMI Resolution	4k30, 1080p120	4k30, 1080p120
Max MHL Resolution	1080p/30Hz, 24 bit (8 bit/color)	1080p/30Hz, 24 bit (8 bit/color)
x.v.Color Support	•	•
HDCP Decryption, HDCP BIST and Pre-programmed HDCP Keys	•	•
CEC Processor	•	•
Advanced Sleep Modes	•	•
Integrated NVRAM EDID for HDMI and VGA Port	•	•
Package Size	176-pin TQFP	176-pin TQFP
Starter Kit	CP9575HDMI	CP9575HDMI

Input Processors

Target Applications: AVR, HTiB

Features	SiI9261
HDMI® Input	4
Analog Video Input	4x 12-bit ADC @ 170MSPS
Display Interface	36-bit
InstaPort™	InstaPort™
Max HDMI Resolution	1080p/60Hz, 36 bit (12 bit/color)
RGB, YCbCr Color Space Conversion	•
x.v.Color Support	•
HDCP Decryption, HDCP BIST and Pre-programmed HDCP Keys	•
CEC Support	•
Hot Plug Support	•
Advanced Sleep Modes	•
Integrated NVRAM EDID for HDMI and VGA Port	4
Repeater Support	•
S/PDIF Compressed Audio	•
Dolby® True HD, DTS-HD, SACD and DVD-audio	•
8-ch I²S Interface @ 192 kHz	•
Master I²C Interface	•
Package Size	208-pin LQFP
Starter Kit	CP9261HDMI/ADC

HDMI Receivers

Target Applications: AVR, HTiB

Features	SiI9233A	SiI9135A
HDMI® Inputs	4	2
RGB Output, YCbCr Output	•	•
Display Interface	36-bit	36-bit
Max HDMI Resolution	1080p/60Hz, 36 bit (12 bit/color)	1080p/60Hz, 36 bit (12 bit/color)
3D Support	•	
RGB, YCbCr Color Space Conversion	•	•
HDCP Decryption, HDCP BIST and Pre-programmed HDCP Keys	•	•
Integrated NVRAM EDID	4	External
Advanced Sleep Modes	•	
Dolby® TrueHD, DTS-HD, SACD and DVD-audio	•	•
4x I²S and SACD DSD Outputs	•	•
DVD-Audio	2/6/8 ch, 32-192kHz	2/6/8 ch, 32-192kHz
Dolby Digital, DTS digital audio	32-96kHz	32-96kHz
Slave I²C Interface	•	•
Auto Video/Audio Mode Detection	•	•
Package Size	144-pin TQFP	144-pin TQFP
Starter Kit	CP9233HDMI	CP9135A

HDMI Transmitters

Target Applications: Blu-ray Disc™, AVR, STB, HTiB

Features	SiI9334	SiI9136-A	SiI9136
RGB Input, YCbCr Input	Up to 48-bit	Up to 48-bit	Up to 48-bit
HDMI Output	1	1	1
Video Resolution	1080p/30Hz, 48 bit (16 bit/color)	4k30p, 1080p120	1080p/30Hz, 48 bit (16 bit/color)
3D Support	•	•	•
Audio Return Channel	•		
HDMI Ethernet Channel	•		
HDCP Encryption, HDCP BIST and Pre-programmed HDCP Keys	•	•	•
Advanced Sleep Modes	•	•	•
S/PDIF Compressed Audio	•	•	•
Dolby® TrueHD, DTS-HD, SACD and DVD-audio	•	•	•
8-ch I²S Interface @ 192 kHz	•	•	•
Master I²C Interface	•	•	•
DE Generator	•	•	•
Package Size	100-pin TQFP	100-pin TQFP	100-pin TQFP
Starter Kit	CP9334HDMI	CP9136HDMI-3	CP9334HDMI

Video Processors

Target Applications: Blu-ray Disc™, AVR, STB, HTiB

Features	ABT1030	ABT1015
Input Formats	36-bit RGB/YCbCr	36-bit RGB/YCbCr
Output Formats	36-bit RGB/YCbCr	36-bit RGB/YCbCr
480i to 1080p Inputs and Outputs	•	•
Pass-through (Including 3D)	•	•
Precision Video Scaling™	•	•
Precision Deinterlacing™	SD	
Progressive Re-Processing (PREP™)	•	
Mosquito Noise Reduction		
Detail/Edge Enhancement		
Deep Color	•	•
x.v.Color Support	•	•
Standard Picture Controls	•	•
Frame Rate Conversion		
On Screen Display		
A/V Lipsync		
Host Interface	I²C	I²C
External Memory	1 SDRAM	
Package Size	176-LQFP	128-LQFP
Starter Kit	CP1030	CP1015

MHL/HDMI-to-HDMI Bridge

Target Applications: PC monitors and projectors

Features	SiI1292
HDMI®/MHL™ Input (Auto detect)	1
HDMI® Output	1
HDCP	•
Video Resolution	HDMI mode: Up to 1080p/60 Hz MHL mode: Up to 1080p/30 Hz
Package Size	40-pin QFN
Starter Kit	CP1292

HDMI/DVI Transmitters

Target Applications: PC motherboards, desktops, notebooks, netbooks, and add-in cards (ADD2)

Features	SiI1392	SiI1364A	SiI1362A	SiI1162	SiI164
HDMI Output	1				
Output Port	HDMI, DVI	1 DVI Port	1 DVI Port	1 DVI Port	1 DVI Port
HDCP	•				
Graphics Controller Interface	SVDO	SVDO	SVDO	12bit (3.3V/1.2V)	12bit-24bit (3.3V/1.2V)
Cable Support	>10 meters	>10 meters	>10 meters		
Microcontroller NOT Required	•	•	•	•	•
HDMI HD Audio / SPDIF	Auto Sense 3.3V-5V				
Video Resolution	Up to UXGA, 1080p/60 Hz	Up to UXGA	Up to UXGA	Up to UXGA	Up to UXGA
Package Size	64-pin QFN	64-pin TQFP/QFN	48-pin LQFP	48-pin TSSOP	64-pin TQFP
Starter Kit	CP1392ADD2	CP1364A	CP1364A	CP1162ADD	N/A

DVI Receivers

Target Applications: LCD monitors/panels, projectors and plasma displays

Features	SiI1161
DVI Input	3.3V
Cable Support	>10 meters
Automatic Power Down	•
Graphics Controller Interface	24bit or 48bit
Video Resolution	Up to UXGA, 1080p/60 Hz
Package Size	100-pin TQFP
Starter Kit	CP1161DVI

Storage Processors

Target Applications: PC motherboards, desktops, notebooks, external enclosures, DAS or NAS boxes, DVRs, and CE equipment

Features	SiI5923	SiI5744	SiI5734	SiI5723	SiI4726
3Gb/s Host and Device Ports	1 host, 2 device	1 host, 2 device	1 host, 2 device	1 host, 2 device	1 host, 5 device
Hardware RAID Modes	0, 1, JBOD	0, 1, JBOD	JBOD	0, 1, JBOD	0, 1, 10, JBOD
BIG or Concatenation Mode		•	•	•	•
USB 2.0 Host Interface		•	•		
SAFE33 and SAFE50 Modes		•			
Multi-RAID Modes		•	•	•	•
GUI Mgmt Applet	•	•	•	•	•
eSATA Support or "Gen2m"	•	•	•	•	•
Status Hardware LED Support	•	•	•	•	•
Hot Plug Support	•	•	•	•	•
Cable Support Up to 2 Meters	•	•	•	•	•
Package Size	40-pin QFN	88-pin QFN	88-pin QFN	88-pin QFN	364-ball HSBGA
Starter Kit	CP5923	PB574402-000	PB573402-000	PB572302-000	PB4726LPSATA300

Host Controllers

Target Applications: PC motherboards, desktop, notebook, server, DVR, video surveillance, CE equipment, HBAs

Features	SiI3531A	SiI3512E	SiI3132	SiI3124A	SiI3114
Device Ports	1	2	2	4	4
SATA Device	3.0Gb/s or Gen2m	1.5Gb/s or Gen1i	3.0Gb/s or Gen2m	3.0Gb/s or Gen2m	1.5Gb/s or Gen1i
Host PCI Bus	x1 PCIe 1.0 / 2.5G	PCI 32bit 33/66MHz	x1 PCIe 1.0 / 2.5G	PCI/X 64bit 33/66MHz	PCI 32bit 33/66MHz
Software RAID Driver	(w/PM 0,1,10, 5)	0, 1	0, 1 (w/PM 10, 5)	0, 1, 10, 5	0, 1, 10, 5
FIS Based Switching	•		•	•	
NCQ	•		•	•	
Vista, Windows 7, 2003, XP, 2K, NT, ME, 98 Support	•	•	•	•	•
MAC OS X			•	•	
Linux Support	•	•	•	•	•
Package Size	48-pin QFN	128-pin TQFP	88-pin QFN	364-ball HSBGA	176-pin TQFP
Starter Kit	PB3531-1ESATA300	PB3512SATA150	PB3132SATA300	PB3124SATA300	PB3114SATA150

Port Multipliers

Target Applications: Server motherboards, PC motherboards, CE motherboards, DVR motherboards, External Enclosures

Features	SiI3826	SiI3726	SiI3723
Host Ports	1 SATA 3Gb/s	1 SATA 3Gb/s	1 SATA 3Gb/s
Device Ports	5 SATA 3Gb/s	5 SATA 3Gb/s	2 SATA 3Gb/s
SEMB Support	•	•	
ESATA Support	•	•	•
Software RAID Compatible	•	•	•
Hot Plug Support	•	•	•
Hardware LED Support	•	•	•
Package Size	208-pin LQFP	364-ball HSBGA	40-pin QFN
Starter Kit	PB3826	PB3726SATA300	CP3723

MHL Transmitters

Target Applications: Mobile phones, tablets, cameras, camcorders and portable media players

Features	SiI9244	SiI9236	SiI9232	SiI8336	SiI8334	SiI8332
HDMI® Input	1				1	
Parallel Digital Video Input		1	1			
MIPI DSI Input				1		1
MHL™ Output	1	1	1	1	1	1
Max Video Resolution	1080p/30Hz, 24 bit (8 bit/color)	1080p/30Hz, 24 bit (8 bit/color)	1080p/30Hz, 24 bit (8 bit/color)	1080p/30Hz, 24 bit (8 bit/color)	1080p/30Hz, 24 bit (8 bit/color)	1080p/30Hz, 24 bit (8 bit/color)
Low Power for Maximum Mobile Battery Life	•	•	•	•	•	•
HDCP Encryption, Pre-programmed HDCP Keys			•			•
Advanced Sleep Modes	•	•	•	•	•	•
Dolby® Digital, DTS Digital Audio		•	•	•		•
8-ch I²S Interface @ 192 kHz		•	•	•		•
DE Generator		•	•	•		•
I²C Interface for Configuration	•	•	•	•	•	•
Package	49-ball BGA	64-ball BGA	64-ball BGA	49-ball BGA	49-ball BGA	49-ball BGA
Starter Kit	CP9244	CP9236	CP9232	CP8336	CP8334	CP8332

MHL-to-HDMI Bridge

Target Applications: Docking stations, converters and adapters

Features	SiI9292
MHL Input	1
HDMI Output	1
Max Video Resolution	1080p/30Hz, 24 bit (8 bit/color)
Low Power for Maximum Mobile Battery Life	•
Package	40-pin QFN
Starter Kit	CP9292

HDMI Transmitters

Target Applications: *Mobile phones, tablets, cameras, camcorders and portable media players*

Features	SiI9024ARBT	SiI9024AYBT	SiI9024ACNU	SiI9022ARBT	SiI9022AYBT	SiI9022ACNU
RGB Input, YCbCr Input	Up to 24-bit	Up to 24-bit	Up to 24-bit	Up to 24-bit	Up to 24-bit	Up to 24-bit
HDMI® Output	1	1	1	1	1	1
Max Video Resolution	1080p/60Hz, 24 bit (8 bit/color)	1080p/60Hz, 24 bit (8 bit/color)	1080p/60Hz, 24 bit (8 bit/color)	1080p/60Hz, 24 bit (8 bit/color)	1080p/60Hz, 24 bit (8 bit/color)	1080p/60Hz, 24 bit (8 bit/color)
Low Power for Maximum Mobile Battery Life	•	•	•	•	•	•
3D Support	•	•	•	•	•	•
HDCP Encryption, Pre-programmed HDCP Keys	•	•	•			
CEC Support	•	•	•	•	•	•
Advanced Sleep Modes	•	•	•	•	•	•
S/PDIF Compressed Audio	•	•	•	•	•	•
Dolby® Digital, DTS Digital Audio	32-96kHz	32-96kHz	32-96kHz	32-96kHz	32-96kHz	32-96kHz
8-ch I²S Interface @ 192 kHz	•	•	•	•	•	•
I²C Interface for Configuration	•	•	•	•	•	•
DE Generator	•	•	•	•	•	•
Package	81-ball BGA	49-ball BGA	72-pin QFN	81-ball BGA	49-ball BGA	72-pin QFN
Starter Kit	CP9024ARBT	CP9024AYBT	CP9024ACNU	CP9022ARBT	CP9022AYBT	CP9022ACNU

HRTX Chipsets

Target Applications: Notebook PC, Tablet, HTiB, AVR, Blu-ray Disc™, Wireless Adapters, STB

Features	SB9220/SB9210
WirelessHD® Standard	V1.0
HRP Channels 2, 3	•
MRP Channel Support	
LRP Channels	3
Max. Video Resolution	1080p/60 4:4:4 24-bit/pixel
3D Video Support	•
LR-Audio (HDMI-ARC)	•
32-192kHz LPCM Audio	•
HDMI® 1.4a Interface	•
30-bit LVCMOS Interface	•
Integrated EDID Support	
RF PA/Antennas	32
Power Rails	1.2V/2.5V
Integrated Buck Controller	
Size	17x17mm/17x21mm
Package	BGA/Ceramic BGA
Starter Kit	Contact Sales

HRRX Chipsets

Target Applications: Plasma HDTV Display, LCD Display, Front Projector, Wireless Adapters

Features	SB9221/SB9211
WirelessHD® Standard	V1.0
HRP Channels 2, 3	•
MRP Channel Support	
LRP Channels	3
Max. Video Resolution	1080p/60 4:4:4 24-bit/pixel
3D Video Support	•
LR-Audio (HDMI-ARC)	•
32-192kHz LPCM Audio	•
HDMI® 1.4a Interface	•
30-bit LVCMOS Interface	•
Integrated EDID Support	
RF PA/Antennas	32
Power Rails	1.2V/2.5V
Integrated Buck Controller	
Size	17x17mm/17x21mm
Package	BGA/Ceramic BGA
Starter Kit	Contact Sales



1140 E Arques Avenue, Sunnyvale, CA 94085
T 408.616.4000 F 408.830.9530
www.siliconimage.com

© Silicon Image, Inc. 2012. All rights reserved. Silicon Image, the Silicon Image logo, InstaPort, TMDS and WirelessHD are trademarks or registered trademarks of Silicon Image, Inc. in the United States, and/or other countries. HDMI is a trademark or registered trademark of HDMI Licensing, LLC in the United States and/or other countries. MHL is a trademark or registered trademark of MHL, LLC in the United States and/or other countries. All other trademarks and registered trademarks are the property of their respective owners in the United States and/or other countries. The absence of a trademark does not constitute a waiver of Silicon Image's trademark or other intellectual property rights with regard to a product name, logo or slogan.