




PCB LAYOUT

Technical data

1.Nominal voltage: 300V/8A
PITCH:3.81mm

2.Insulation Withstanding Voltage:
AC1600V/MIN

3.Insulation Resistance:
1000MΩ or more at DC500V

4.Operating temperature range:-40°C~115°C

5.Soldering temperature range:250°C±10°C/5sec

6.Safety approval:

7.RoHS Compliance

8.Undimensioned Tolerances:

Dim.L=(P-1)x3.81+5.0 Dim.B=(P-1)x3.81 P= number of poles		
0-30mm	±0.15	±0.20
over 30mm-60mm	±0.20	±0.25
over 60mm-90mm	±0.25	±0.30
over 90mm	±0.30	±0.40

Part No.:

OSTOQXX3250

No. of Poles

02 2 Poles

03 3 Poles

... ..

24 24 Poles

COLOR

0: Black

2: Red

3: Orange

4: Yellow

5: Green (Standard)

6: Blue

8: Grey

Nonstandard colors
Mins could apply

2	PIN	BRASS	TIN PLATED	P
1	BODY	PA66 UL94V-0		1
ITEM	NAME OF PART	MATERIAL	NOTES	Q"TY
DWG.	WF. Zhang	DATE 2016.03.31	UNITS: MM	SHEET: 1 OF 1
CHK.	WF. Zhang	DATE 2016.05.21	SCALE: NONE 4:1 (:)	REV.: A
APP.		DATE	TITLE: OSTOQ 3.81 Series	X. ±0.50
			Close type Vertical(180D)	X.X ±0.30
			PART NO. OSTOQXX3250	X.XX ±0.10
			DWG NO. OSTOQXX3250.dwg	X* ±1°
ON-SHORE TECHNOLOGY, INC.				

△	DESCRIPTION	CHK.	DATE
SIGN			