



- ErP<sup>1</sup>, CEC<sup>2</sup> and EISA<sup>3</sup> Compliant Models
- Wide Range AC Input
- Medical Certifications

## Key Market Segments & Applications

Medical, Industrial Computing,  
Life Sciences / Laboratory

# DTM65-C Series

60W to 65W Medical AC-DC External Power Supplies

## DTM65-C Features and Benefits

### Features

- CEC and EISA Compliant
- Wide Range AC Input
- 87% Average Efficiency

### Benefits

- Easier system compliance
- Global Operation
- Consumes less energy


### Specifications

ITEMS		DTM65-C
Input Voltage Range		90 - 264VAC (47 - 63Hz)
Inrush Current	A	100A at 230VAC input, 25°C ambient cold start
Input Current	A	2A at 90VAC, Full Load
Power Factor		None
Leakage Current (264VAC 63Hz)	mA	<300uA
Hold Up Time (Typ)	ms	16ms at 230VAC input
Temperature Coefficient		±0.05%/°C
Voltage Accuracy	%	±1%
Adjustment Range		None
Minimum Load	A	None
Total Regulation		12V Model: ±5%, >15V models ±3%
Ripple & Noise	%	1% or 100mV whichever is the greater
Short Circuit Protection	-	Continuous - hiccup mode
Overvoltage Protection	V	110 - 150% of nominal (Cycle input power to reset)
Average Efficiency	%	87%
Operating Temperature	°C	0 to +50°C
Storage Temperature	°C	-10 to +70°C
Humidity (non condensing)		10 - 90% RH
Cooling	-	Convection
Withstand Voltage		Input to Ground 1.5kVAC, Input to Output 4kVAC (Output is connected to Ground)
Vibration (non operating)		23.52m/s <sup>2</sup> (10 - 55Hz: constant sweep 1 min X, Y, Z for 1 hour)
Shock		< 196.1 m/s <sup>2</sup> (20G)
Safety Agency Approvals	-	CE, UL60601-1, EN60601-1, IEC60601-1
Safety Class	-	Class I
Altitude	m	3000m
Offload Power Consumption	W	< 0.5W
Conducted & Radiated EMI		EN60601-1-2, FCC Part 18 Class B
Immunity		EN55011
Weight (Typ)	g	460g
Size (WxLxH)	mm	69 x 132 x 39.9
Cable Length	mm	1050mm
AC Input Connector		IEC 320-C14 (Accepts IEC 320-C13)
Output Connector		Kycon KPPx-4P or equivalent, Pins 1 & 2: -Vout, Pins 3 & 4: +Vout
Warranty	yrs	2

Notes: (1) ErP - Energy Related Products (2) Californian Energy Commission (3) EISA - Energy Independence and Security Act of 2007


Model Selector						
Model	Output (V)	Maximum Output (A)	Maximum Power (W)	ErP	CEC	EISA Efficiency Level
DTM65PW120C	12	5.0	60	Step 2	V	V
DTM65PW150C	15	4.0	60	Step 2	V	V
DTM65PW180C	18	3.6	65	Step 2	V	V
DTM65PW240C	24	2.7	65	Step 2	V	V
DTM65PW360C	36	1.8	65	Step 2	V	V
DTM65PW480C	48	1.35	65	Step 2	V	V

**Outline Drawing DTM65-C Series**



Other External AC-DC Products - **DTM110-C, DTM165, DTM65-C8**

## DTM65-C Output Connector



### Pinout DTM65-C Model

Pin	Function
1	- Vout
2	- Vout
3	+ Vout
4	+ Vout

Alternative output connectors are available  
Please contact Sales for further information (min quantities apply)



**TDK-Lambda France SAS**

3 Avenue du Canada  
 Parc Technopolis  
 Bâtiment Sigma  
 91940 les Ulis  
 France  
 Tel: +33 1 60 12 71 65  
 Fax: +33 1 60 12 71 66  
[france@fr.tdk-lambda.com](mailto:france@fr.tdk-lambda.com)  
[www.fr.tdk-lambda.com](http://www.fr.tdk-lambda.com)



**Italy Sales Office**

Via dei Lavoratori 128/130  
 20092 Cinisello Balsamo (MI)  
 Italy  
 Tel: +39 02 61 29 38 63  
 Fax: +39 02 61 29 09 00  
[info.italia@it.tdk-lambda.com](mailto:info.italia@it.tdk-lambda.com)  
[www.it.tdk-lambda.com](http://www.it.tdk-lambda.com)



**Netherlands**

[info@nl.tdk-lambda.com](mailto:info@nl.tdk-lambda.com)  
[www.nl.tdk-lambda.com](http://www.nl.tdk-lambda.com)



**TDK-Lambda Germany GmbH**

Karl-Bold-Strasse 40  
 77855 Achem  
 Germany  
 Tel: +49 7841 666 0  
 Fax: +49 7841 5000  
[info.germany@de.tdk-lambda.com](mailto:info.germany@de.tdk-lambda.com)  
[www.de.tdk-lambda.com](http://www.de.tdk-lambda.com)



**Austria Sales Office**

Aredstrasse 22  
 2544 Leobersdorf  
 Austria  
 Tel: +43 2256 655 84  
 Fax: +43 2256 645 12  
[info@at.tdk-lambda.com](mailto:info@at.tdk-lambda.com)  
[www.de.tdk-lambda.com](http://www.de.tdk-lambda.com)



**Switzerland Sales Office**

Bahnhofstrasse 50  
 8305 Dietlikon  
 Switzerland  
 Tel: +41 44 850 53 53  
 Fax: +41 44 850 53 50  
[info@ch.tdk-lambda.com](mailto:info@ch.tdk-lambda.com)  
[www.de.tdk-lambda.com](http://www.de.tdk-lambda.com)



**Nordic Sales Office**

Haderslevvej 36B  
 DK-6000 Kolding  
 Denmark  
 Tel: +45 2911 9556  
[info@dk.tdk-lambda.com](mailto:info@dk.tdk-lambda.com)



**TDK-Lambda UK Ltd.**

Kingsley Avenue  
 Ilfracombe  
 Devon EX34 8ES  
 United Kingdom  
 Tel: +44 (0) 12 71 85 66 66  
 Fax: +44 (0) 12 71 86 48 94  
[powersolutions@uk.tdk-lambda.com](mailto:powersolutions@uk.tdk-lambda.com)  
[www.uk.tdk-lambda.com](http://www.uk.tdk-lambda.com)



**TDK-Lambda Ltd.**

Kibbutz  
 Givat Hashlosha 48800  
 Israel  
 Tel: +9 723 902 4333  
 Fax: +9 723 902 4777  
[info@tdk-lambda.co.il](mailto:info@tdk-lambda.co.il)  
[www.tdk-lambda.co.il](http://www.tdk-lambda.co.il)



**C.I.S.**

**Commercial Support:**  
 Tel: +7 (495) 665 2627  
**Technical Support:**  
 Tel: +7 (812) 658 0463  
[info@tdk-lambda.ru](mailto:info@tdk-lambda.ru)  
[www.tdk-lambda.ru](http://www.tdk-lambda.ru)

**Local Distribution**

