

LVR

Art.-No. 344-00160 | LVR-1.6/0.8-PVC-BK | [Details](#)



This product is not available anymore.
Please contact our sales team. >

- PVC heat shrinkable tubing
- Self-extinguishing
- Good chemical resistance and mechanical protection


RoHS 

 Add to watchlist

 Downloads

 Datasheet

More products in this product group:
[Heat shrinkable tubing 2:1 - PVC >](#)



Base Data Product Dimensions Downloads

Application	LVR can be used for cable joints, low voltage bus bars and batteries.
Application Tool	H6100
Colour	Black (BK)
Material	Flexible Polyvinyl Chloride, cadmium free (PVC)
Pack Cont.	250 m
Package Content packed in	metre
PART DESCRIPTION	LVR-1.6/0.8-PVC-BK
Printable	No
Product Family	LVR
Product Group	Heat shrinkable tubing 2:1 - PVC
Shrink Ratio	2:1
Size	1/16 "
Variant	Thin-Wall
With inner glue (Yes/No)	No


Specifications Logistics and Packaging More Information

Dielectric Strength	22 kV/mm
ELV compliant (Article 4 - 2)	YES
Flammability	ASTM D2671
Hazardous Goods	No
Min. Shrink Temperature - °C	+80 °C
Operating Temperature	-30 °C to +105 °C
Shelf Life	12 months
Specifications	RoHS 

Calculators



Calculator tool for Heat Shrink Tubing



Wall thickness calculator

Accessories

H6100
391-00110
Electrical Hot Air Tool

 Add to watchlist

Similar products



LVR-4.8/2.4
344-00480
Heat shrinkable tubing 2:1 - PVC

 Add to watchlist



LVR-6.4/3.2
344-00640
Heat shrinkable tubing 2:1 - PVC

 Add to watchlist



LVR-9.5/4.8
344-00950
Heat shrinkable tubing 2:1 - PVC

 Add to watchlist



LVR-2.4/1.2
344-00240
Heat shrinkable tubing 2:1 - PVC

 Add to watchlist



LVR24
344-20300
Heat shrinkable tubing 2:1 - PVC

 Add to watchlist



LVR-2.4/1.2
344-20301
Heat shrinkable tubing 2:1 - PVC

 Add to watchlist

Show all ▾

Competences



Insulating tubes

From neoprene sleeves and silicone tubes to PTFE or PVC hoses: Find the right insulating tubing and accessories for your application now.

[Insulating tubes >](#)

Stay in touch with us!

