
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION – ,– .
© COPYRIGHT – By – ALL RIGHTS RESERVED.

LOC	DIST
DW	—


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REVISED (ECR–13–008834)	11SEP2013	B.W	H.K


–3 : AS SHOWN





DETAIL C
(SCALE 4:1)




DETAIL D
(SCALE 4:1)








BUTTON COLOR:
GRAY(1759880–1)
BLACK(1759880–3)





DETAIL E
(SCALE 4:1)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± 0.3
1 PLC	± 0.25
2 PLC	± 0.25
3 PLC	± –
4 PLC	± –
ANGLES	± 1°

MATERIAL: –
FINISH: –

DWN	S.WATANABE	15AUG07
CHK	J.CHIANG	15AUG07
APVD	H. KODAMA	15AUG07

PRODUCT SPEC: –
APPLICATION SPEC: –
WEIGHT: 18GRAM

CUSTOMER DRAWING

TE Connectivity

NAME
EXPRESS CARD CONNECTOR
SHIELD FRAME ASSEMBLY, TOP MOUNT
–

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C–1759880	–

SCALE	SHEET	REV
1:1	1 OF 4	D1

1470–19 (3/11)

Downloaded from Arrow.com.


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,– .
© COPYRIGHT – By – ALL RIGHTS RESERVED.


LOC	DIST
DW	–


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	–	SEE SHEET 1	–	–	–


–3 : AS SHOWN








REFERENCE FIGURE WHICH ATTACHED
HEADER ASSEMBLY



H–H
SCALE 2:1



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± 0.3
1 PLC	± 0.25
2 PLC	± 0.25
3 PLC	± –
4 PLC	± –
ANGLES	± 1°

MATERIAL | FINISH –

DWN | CHK | APVD | PRODUCT SPEC – | APPLICATION SPEC – | WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME
EXPRESS CARD CONNECTOR
SHIELD FRAME ASSEMBLY, TOP MOUNT

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C–1759880	–

SCALE	SHEET	REV
1:1	2 OF 4	D1

1470–19 (3/11)

Downloaded from Arrow.com.


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,– .
© COPYRIGHT – By – ALL RIGHTS RESERVED.

LOC	DIST
DW	–


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	–	SEE SHEET 1	–	–	–


–3 : AS SHOWN




RECOMMAND PWB LAYOUT



DETAIL B
(SCALE 2:1)



DETAIL F
SCALE 2:1



DETAIL G
SCALE 2:1

OBSOLETE

ITEM	NAME	MATERIAL	FINISH	1759880–3	1759880–2	1759880–1	Q'TY
				COLOR			
⑧	BUSH (M2X0.4 TAP)	STAINLESS STELL					2
⑦	ARM BAR	STAINLESS STELL					1
⑥	BRACKET (R) (M2X0.4 TAP)	STAINLESS STELL					1
⑤	BRACKET (L) (M2X0.4 TAP)	STAINLESS STELL					1
④	GUIDE RAIL HSG	THERMOPLASTIC (UL94 V–0)		BLACK	BLACK	BLACK	1
③	LOWER SHELL	STAINLESS STELL					1
②	UPPER SHELL	STAINLESS STELL					1
①	PUSH PUSH ASSY	STAINLESS STELL					1
		THERMOPLASTIC (UL94 V–0)		BLACK	GRAY	GRAY	

NOTES:
1. RECOMMANDED TIGHTENING TORQUE 0.15~0.2Nm
2. SOLDERING PAD
3. GROUNDING PAD
4. NO COMPONENT AND NO SIGNAL LINE AREA
5. STAND OFF 0.45mm
6. STAND OFF 0.85mm
7. STAND OFF 3.25mm
8. M2 SCREW LENGTH
9. HEADER ASS'Y, 1759878–1, PURCHSED SEPARATELY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± 0.3
1 PLC ± 0.25
2 PLC ± 0.25
3 PLC ± –
4 PLC ± –
ANGLES ± 1°

MATERIAL –
FINISH –

DWN
CHK
APVD
PRODUCT SPEC –
APPLICATION SPEC –
WEIGHT –
CUSTOMER DRAWING

TE Connectivity

NAME
EXPRESS CARD CONNECTOR
SHIELD FRAME ASSEMBLY, TOP MOUNT

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C–1759880	–

SCALE	SHEET	REV
1:1	3 OF 4	D1

Downloaded from Arrow.com.


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,– .
© COPYRIGHT – By – ALL RIGHTS RESERVED.


LOC	DIST
DW	–


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	–	SEE SHEET 1	–	—	—


EJ ASSEMBLY










–3 : AS SHOWN









10. PACKING MATERIAL :
TRAY : PS
SHIPPING CARTON : CORRUGATED FIBERBOARD

16	10	160
PCS/TRAY	TRAY/CARTON	TOTAL QTY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± 2
1 PLC	± 1
2 PLC	± 1
3 PLC	± –
4 PLC	± –
ANGLES	± 3°

MATERIAL –

FINISH –

DWN
CHK
APVD
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT —

CUSTOMER DRAWING

TE Connectivity

NAME
EXPRESS CARD CONNECTOR
SHIELD FRAME ASSEMBLY, TOP MOUNT

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1759880	—

SCALE	SHEET	REV
1:1	4 OF 4	D1

Downloaded from Arrow.com.