




used for:	D-SUB
-----------	-------

AT ALL TIMES WATER RESISTANT CONNECTORS NOT IN USE SHOULD BE COVERED WITH A CONEC WATER RESISTANT CAP OR WATER TIGHT HOOD.

No. of pos.	A ^{+0.2}	B ^{+0.2}	C	D ^{-0.25}	PART NO.
9	21.1	39.4	25.00 ^{+0.12} _{-0.13}	16.46	4STD09SCR99B30X
15	21.1	47.7	33.30 ^{+0.15} _{-0.1}	24.79	4STD15SCR99B30X
25	21.1	61.4	47.04 ^{+0.1} _{-0.13}	38.50	4STD25SCR99B30X
37	21.1	77.9	63.50 ^{+0.13} _{-0.15}	54.96	4STD37SCR99B30X



⑥ NOTES:

1. METALSHELLS: COPPER ALLOY; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
PLATING: 30µin HARD GOLD OVER min. 50µin NICKEL
4. THREADED INSERT: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
5. COLLAR: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
6. HEXLOCKING SCREW: STAINLESS STEEL
7. P.C.B. HOLE DRILLINGS ON SHEET 2
8. RECOMMENDED TORQUE FOR MOUNTING SCREW 35N cm (3.1 in.LB) / max. 40N cm (3.5 in.LB)
9. CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

Directive 2002/95/EC
"RoHS"
Compliant

APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL


THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance	
				dim. in mm	
				2000	date
				drawn	20.03. A. Mickenbecker
				appd.	20.03. E. Mickenbecker
				norm	DIN 41652
				d-old	
3xb	Ä2712	31.05.07	son.		
a	Origin				
rev.	description	date	name		







scale:		2:1	
material:		SEE NOTES	
title:			
D-SUB FEMALE			
9-37pos. SOLDER PIN STRAIGHT			
with threaded insert and hexlocking screw			
dwg no:		AutoCAD 2006	DIN-A
18K11G3A			3
			sh:1/2
part no:		SEE TABLE	




used for: D-SUB




9 pos.



15 pos.



25 pos.



37 pos.

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		

tolerance	dim. in mm
2007	date
drawn	31.05.
appd.	31.05.
norm	DIN 41652
d-old	

scale: 2:1
material: SEE SHEET 1
title: P.C.B. HOLE DRILLINGS D-SUB FEMALE 9-37pos. SOLDER PIN with threaded insert and hexlocking screw
dwg no: AutoCAD 2006
part no: SEE SHEET 1

