




Directive 2002/95/EC
„RoHS“
Compliant



1. MATERIAL:
Insulator: Thermal Plastic UL94V-0
CONTACTS: COPPER ALLOY
SHELL: STEEL
RIVET:BOARDLOCK: COPPER ALLOY
2. CONTACT PLATING
Underplate: 50µin NICKEL
Contact Area: Gold Flash
Solder Tails Area: 100µin TIN / Lead free
3. ELECTRICAL:
Operation Voltage: 250 VAC max.
CURRENT RATING: 3 Amps max.
CONTACT RESISTANCE: 15 mohms min.@ 500 VDC
DIELECTRIC WITHSTANDING VOLTAGE: 1000VAC / minute
OPERATING TEMPERATURE: -55°C to +105°C
4. CONNECTOR IS PART MARKED: DLH1XS8AK53X CONEC ABC

RECOMMENDED P.C.B LAYOUT (TOP VIEW)
TOLERANCES: $\pm 0.1\text{mm}$

APPROVAL # FREIGABE # DEBLOCAGE # AUTOD/ZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCAGE # AUTOD/ZACION # APPROVAL	
	CUSTOMER APPROVAL DATE:	
	NAME:	TITLE:
	COMPANY NAME:	
	APPROVAL # FREIGABE # DEBLOCAGE # AUTOD/ZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.

				tolerance ANG. $\pm 5^\circ$ G. ± 0.5 .0 ± 0.3 .00 ± 0.2		 dim. in mm	
				2008	date	name	
				drawn	08.10.	Sonnenberg	
				appd.	08.10.	Mickenbecker	
				norm			
				d-old			
a	Origin						
rev.	description		date				

tolerance	
ANG.	$\pm 5^\circ$
0.	± 0.5
.0	± 0.3
.00	± 0.2



dim. in mm

scale:	2:1
material:	SEE SPECIFICATION

title:	D-SUB HD FEMALE 90° R/A 15pos. with snap-in, clinch nut
--------	---

dwg no:	AutoCAD 2006	DIN-A
16K1A2375		3
		sh: 1/1
part no:	DLH1XS8AK53X	