




- NOTES
- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-PRF-8805, SYMBOL 4
 - 3 - CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
 - 4 - UNIT PROVIDES NO SHAFT RESTORING TORQUE. THE ACTUATING DEVICE MUST CONTROL MOVEMENT OF THE SHAFT
 - 5 - DO NOT APPLY MORE THAN 20-25 INCH-POUNDS OF TORQUE WHEN TIGHTENING LOCKING NUT
 - 6 - LEADS PARALLEL WITH CENTERLINE OF MOUNTING PINS WITHIN ±10°
 - 7 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805
 - 8 - POTTING MATERIAL
 - 9 - FREE TO ROTATE
 - 10 - .050 WIDE X .050 DEEP SLOT
 - 11 - Ø.037 HOLE FOR WIRE LOCKING



44EN14-10
 M
 17
 REVISIONS
 A 76587 5 NOV 93
 B 78255 1 SEP 94
 C 0008133 28 SEP 04
 T S M 5 NOV 93
 RASTER

CHARACTERISTICS	ELECTRICAL DATA	
OPERATING TORQUE --- 10 IN-LB MAX	CONTACT ARRANGEMENT (SEE CIRCUIT DIAGRAM)	
PRETRAVEL	28 VDC	
DIFFERENTIAL TRAVEL	SEE DETAIL	
OVERTRAVEL	SEE DETAIL	
FREE POSITION	SEE DETAIL	
	LOAD	
	RES	SEA LEVEL 50,000 FT
	IND	15 15
	MOTOR	10 10
	LAMP	5 3

MASTER REDUCED
ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

MICRO SWITCH
a Honeywell Division

SWITCH-ENCLOSED

CATALOG LISTING
44EN14-10

FED. MFG. CODE 91929

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE (.0)	±.030
TWO PLACES (.00)	±.015
THREE PLACES (.000)	±.005
ANGLES	±

WEIGHT **16.5 OZ MAX**