


MAG-MATE TERMINALS WITH MULTISPRING PIN

SAY GOODBYE TO MAGNET WIRE SOLDERING AND PCB SOLDERING

The MAG-MATE terminal with Multispring pin combines two key technologies to eliminate the need to solder in a motor connection. It provides the ability to directly connect magnet wire to a PCB with no solder. Traditionally, the process is to solder magnet wire to a pin, assemble the PCB to the pin, and then solder the PCB to the pin. Not anymore! This product allows solderless magnet wire termination with an insulation displacement contact (IDC) at the bottom and solderless PCB termination through press-fit Multispring pin on the top.

KEY BENEFITS



Features of the Multispring pin

- Large gas-tight contact zone
- High reliability due to stored energy
- Minimum damage to plated-through holes during application
- Especially suited for multi-layer PCBs
- More economic board manufacturing due to larger hole tolerances compared to the use of a solid pin
- Application can be made by the end-user
- High-end TE Connectivity application tooling available
- Extraction force: Pin/PCB min 40N

Features of the MAG-MATE Terminal

- Eliminates need for pre-stripping conductors
- Eliminates need to solder/weld
- Excess magnet wire is automatically trimmed during the termination process
- Simultaneously terminates two magnet wires of the same size in one terminal (for splicing or bi-filing)
- Available in strip form for either semi-automatic or fully-automatic insertions
- High speed, fully-automated integrated systems provide uniform terminations reliably at a very low applied cost
- Clean metal-to-metal interface produces stable, gas-tight electrical terminations free of oxides and other contaminants

APPLICATIONS

Any motor or other magnet wire application that requires a direct PCB connection.

SPECIFICATIONS

Product Specification: [108-74116](#)

Application Specification: [114-74109](#)

MAG-MATE TERMINALS WITH MULTISPRING PIN

COPPER WIRE

Diameter (mm)	Standard PN	Slim Line PN*
0.180-0.265	1247000-2	2120743-2
0.265-0.400	1247001-2	2120744-2
0.400-0.630	1247002-2	2120745-2
0.630-0.850	1247003-2	2120746-2
0.850-1.120	1247004-2	2120747-2
1.20-1.30	2238145-2	-

* For slim line MAG-MATE terminals with Multispring pin for aluminum magnet wire, please consult TE Connectivity.

ALUMINUM WIRE

Diameter (mm)	PN
0.32-0.45	1247001-3
0.57-0.72	1247002-3
0.72-0.91	1247003-3
0.95-1.15	1247004-3
1.30-1.45	2238145-3

te.com

TE Connectivity, TE, TE connectivity (logo), MAG-MATE and Multispring are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

© 2023 TE Connectivity. All Rights Reserved.

06/23