





PRODUCT NUMBER	PITCH
VExx30x000J0G	3.81 mm


 RECOMMENDED P.C.B LAYOUT
 TOP VIEW


Material:

- Item ③ Contact pin: Copper, Tin plated
- Item ⑥ Terminal(housing): Thermoplastic (UL94V-0)

Electrical:

- Voltage rating: 300V
- Current rating: 8A
- Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus

DIMENSION

Dim A	Nx3.81
Dim B	(N-1)X3.81

N= NUMBER OF POLES

Poles	Tolerance
2P-5P	±0.15
6P-10P	±0.20
11P-15P	±0.25
16P-20P	±0.30
21P-24P	±0.35

PART NO.: VE xx 30 x 0 00J0 G

Solid block	No. of poles	Color	RoHS compliant
02	2 poles	0 Black (RAL9005)	(lead<4%)
03	3 poles	2 Red (RAL3001/D)	In copper Alloy
...	...	3 Orange(RAL2011/P)	
24	24 poles	4 Yellow(RAL1018/A)	
		5 Green(RAL6018/T)	
		6 Blue (RAL5015/A)	
		8 Grey(RAL7035/D)	
		9 White(RAL1102)	
		C Green(RAL6018/U)	

mat'l. code				surface	tolerance	projection	product family	
ltr	ecn	no	dr	date	ASME Y14.5	ASME Y14.5	TERMINAL BLOCK	
					tolerances unless otherwise specified		title	
					angles	X.±0.5	TERMINAL BLOCK	
					fil	X.X±0.3	PLUGGABLE SOCKET, OPEN VERTICAL	
					X'±1"	X.XX±0.1	scale	
					dr	EVIN ZHONG 042214	dwg no	
					enr	EVIN ZHONG 042214	sheet 1 of 1	
					chr	HANKE FENG 042214	VExx30x000J0G	
					appd	SHI JUN 042214	type	
							CUSTOMER Drawing	
sheet index	revision	A						
	sheet	1						