

SACC-VB-4CON-M16/A - Valve connector



1452136

<https://www.phoenixcontact.com/us/products/1452136>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Valve connector, Universal, 4-position, Valve connector AD (pressure switch), Screw connection, cable gland M16, external cable diameter 6 mm ... 8 mm

Commercial data

| | |
|--------------------------------------|--------------------|
| Item number | 1452136 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF36 |
| Product key | AF2DAA |
| Catalog page | Page 28 (C-2-2019) |
| GTIN | 4046356536301 |
| Weight per piece (including packing) | 27.4 g |
| Weight per piece (excluding packing) | 27.4 g |
| Customs tariff number | 85366990 |
| Country of origin | HU |

SACC-VB-4CON-M16/A - Valve connector



1452136

<https://www.phoenixcontact.com/us/products/1452136>

Technical data

Notes

| | |
|---------------|---|
| Assembly note | NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties. |
|---------------|---|

Product properties

| | |
|----------------------|------------------|
| Product type | Valve connectors |
| Sensor type | Universal |
| Number of positions | 4 |
| No. of cable outlets | 1 |
| Shielded | no |
| Pg screw connection | M16 |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 3 |

Material specifications

| | |
|--|------|
| Flammability rating according to UL 94 | HB |
| Seal material | NBR |
| Material housing valve plug | PA |
| Contact material | CuZn |
| Contact surface material | CuSn |

Dimensions

| | |
|---------------------|---------|
| Dimensional drawing | |
| Width | 28 mm |
| Height | 31.5 mm |
| Length | 50 mm |

External dimensions

| | |
|------------------|---------------|
| Outside diameter | 6 mm ... 8 mm |
|------------------|---------------|

Electrical properties

| | |
|--------------------------------|----------|
| Contact resistance | ≤ 4 mΩ |
| Insulation resistance | > 2 GΩ |
| Nominal voltage U _N | 230 V AC |
| | 230 V DC |

SACC-VB-4CON-M16/A - Valve connector



1452136

<https://www.phoenixcontact.com/us/products/1452136>

| | |
|-----------------------|---------|
| Nominal current I_N | 10 A |
| Protective circuit | unwired |

Valve connector characteristics

| | |
|---------------|-----------|
| Fixing screws | M3 x 33,5 |
|---------------|-----------|

Mechanical properties

Mechanical data

| | |
|-----------------------------|----------------------|
| Insertion/withdrawal cycles | 50 (Valve connector) |
|-----------------------------|----------------------|

Signaling

| | |
|------------------------|----|
| Status display present | no |
|------------------------|----|

Connection data

| | |
|------------------------------|--|
| Connection method | Screw connection |
| Conductor cross section | 0.25 mm ² ... 1.5 mm ² |
| Connection cross section AWG | 24 ... 16 |
| Tightening torque | 1.8 Nm ±0.2 Nm (Pressure screw) |
| | 0.4 Nm ±0.1 Nm (Central screw) |
| | 0.2 Nm ±0.1 Nm (Contact screw) |

Connector

Connection 1

| | |
|------------------|----------------------|
| Head design | Valve connector |
| Head thread type | AD (pressure switch) |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------------------------|
| Degree of protection | IP65 |
| Ambient temperature (operation) | -25 °C ... 60 °C (Valve connector) |

Standards and regulations

| | |
|--------------------------|-----------------|
| Standard designation | Valve connector |
| Standards/specifications | EN 175301-803 |

SACC-VB-4CON-M16/A - Valve connector


1452136

<https://www.phoenixcontact.com/us/products/1452136>




Drawings

Dimensional drawing



Circuit diagram



SACC-VB-4CON-M16/A - Valve connector



1452136

<https://www.phoenixcontact.com/us/products/1452136>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1452136>



EAC

Approval ID: RU C-DE.AI30.B.01102



EAC

Approval ID: EAC-Zulassung

SACC-VB-4CON-M16/A - Valve connector



1452136

<https://www.phoenixcontact.com/us/products/1452136>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440105 |
|-------------|----------|

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC003623 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31251500 |
|-------------|----------|

SACC-VB-4CON-M16/A - Valve connector



1452136

<https://www.phoenixcontact.com/us/products/1452136>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-25 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 47f84b54-5cac-4f10-918c-dd4f48113a8f |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com