

NOTES:
1. MATERIALS AND FINISHES:
   BODY - BRASS, NICKEL PLATING
   BARREL - BRASS, NICKEL PLATING
   CONTACT - PHOSPHOR BRONZE, GOLD PLATING
   FERRULE - COPPER, NICKEL PLATING
   INSULATOR - PTFE, NATURAL
2. ELECTRICAL;
   A. IMPEDANCE:50 OHM
   B. FREQUENCY RANGE: DC-11 GHz
   C. DIELECTRIC WITHSTANDING VOLTAGE: 2500 VRMS, MIN.
3. MECHANICAL:
   A. DURABILITY: 500 CYCLES MIN.
   B. TEMPERATURE RANGE: -65° TO +165°
4. CRIMPED FERRULE
   HEX. CRIMP SIZE .213"
5. CRIMPED CONTACT PIN
   HEX. CRIMP SIZE .100"
   OR CONTACT PIN TO SOLDER

THIRD ANGLE PROJ.


REVISIONS				
REV	DESCRIPTION	DATE	ECO	APPR
A	PRELIMINARY RELEASE	18-Aug-00	43503	KERRY
E	REDRAWN IN PROE	07-Feb-12	48929	DH
F	THE CONTACT PIN WAS CHANGED\RD-DM1207110IM	18-Jul-12	49194	DH
G	THE BARREL WAS CHANGED\RD-DM1208070IM	16-Aug-12	49194	SH





RECOMMENDED
CABLE STRIPPING DIM'S



SCALE 1.000







CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:

<0.5mm	0.5 - 6mm	6 - 30mm	30 - 120mm	ANGLES
± 0.05mm	±0.1mm	±0.2mm	± 0.3mm	±1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon requiest; and (3) arre confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the funishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implicatioin or otherwise in any manner licensing, granting rights to permitting such holder or any other sperson to manufacture, use or sell any product, process or design, patented or otherwsie, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL
-

REFERENCE

FINISH

DRAWN M.ZHANG — DATE 16-Aug-12
ENGINEER S.LI — DATE 03-Feb-12
APPROVED S.HSIEH — DATE 16-Aug-12
CAD FILE I:\N\N6121AI-NT3G-58CU-50

TITLE
N CRIMP JACK
FOR RG-58,141 &
142 CABLES,50 OHM

SCALE: 4.0:1.0 | SHEET 2 OF 2
DWG SIZE B | REV G

Amphenol RF
Danbury CT USA, Tainan, Taiwan, Shenzhen, China
www.amphenolrf.com

DRAWING NO.N6121AI-NT3G-58CU-50
ITEM NO. 06121AAA57NA5F
PART NO. 82-5376-RFX

Downloaded from Arrow.com.