



**Part Number :** [894858001](#)

**Product Description :** Universal Serial Bus (USB) Shielded I/O Type A Receptacle, Single Upright, Right-Angle, Terminal Length 2.00mm, Without Mylar, 0.76µm Gold (Au) Plating, Tray Package, Lead-Free

**Series Number :** 89485

**Status :** Active

**Product Category :** I/O Connectors



---

## Documents and Resources

### Drawings

[894858001\\_sd.pdf](#)

[PK-89485-002-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications


[673290000-AS-000.pdf](#)

[PS-89485-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	I/O Connectors
Series	89485
Description	Universal Serial Bus (USB) Shielded I/O Type A Receptacle, Single Upright, Right-Angle, Terminal Length 2.00mm, Without Mylar, 0.76µm Gold (Au) Plating, Tray Package, Lead-Free
Application	Wire-to-Board
Comments	Without Mylar
Component Type	Receptacle
Product Name	USB
Standard	USB 2.0
Type	A
UPC	822348695850

### Agency

CSA	LR19980
UL	E29179

### Electrical

Current - Maximum per Contact	1.0A
Shielded	Yes
Shield Type	Full Shield
Voltage - Maximum	750V AC (RMS)

## Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Flammability	94V-0
Gender	Female
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Mounting Style	Upright
Net Weight	2.259/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
PC Tail Length	2.00mm
Pitch - Mating Interface	2.00mm, 2.50mm
Pitch - Termination Interface	1.40mm
Plating min - Mating	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Through Hole
Waterproof / Dustproof	No

## Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE
Max-Cycle	2
Max-Temp	260

---

This document was generated on Jun 02, 2026