

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0901210766

Status:

Active

Overview:

C-Grid III Interconnects

Description:

2.54mm Pitch C-Grid III Header, Single Row, Right-Angle, 6 Circuits, 0.38µm Gold (Au) Selective Plating

Documents:

3D Model

Drawing (PDF)

Product Specification PS-99020-0001-001 (PDF)

Application Specification 901190001-AS-000 (PDF)

Packaging Specification PK-90120-100-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	PCB Headers
Series	90121
Application	Signal, Wire-to-Board
Component Type	PCB Header
Overview	C-Grid III Interconnects
Product Name	C-Grid III
Taxonomy	PCB Headers and Receptacles
UPC	800753706347

Physical	
Breakaway	Yes
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	0.463/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	2.90mm
PCB Locator	No
PCB Retention	None
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.381µm
Plating min - Termination	3.048µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	No
Temperature Range - Operating	-55° to +125°C
Termination Interface: Style	Through Hole



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained per - D(2022)9120-DC (17 Jan 2023)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

90121 Series

Mates With

C-Grid III Vertical PCB Receptacle 90147 . C-Grid III Right-Angle PCB Receptacle 90148 . C-Grid III Modular Crimp Housing 90123

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	350V

Solder Process Data

Duration at Max. Process Temperature (seconds)	003
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235

Material Info

Reference - Drawing Numbers

Application Specification	901190001-AS-000
Packaging Specification	PK-90120-100-001
Product Specification	PS-99020-0001-001
Sales Drawing	SD-90121-001-001

This document was generated on 03/21/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION