

Silicon Carbide (SiC) MOSFET – EliteSiC, 12 mohm, 650 V, M3S, TOLL

NTBL012N065M3S

Features

- Typical $R_{DS(ON)} = 12\text{ m}\Omega$ @ $V_{GS} = 18\text{ V}$
- Ultra Low Gate Charge ($Q_{G(tot)} = 143\text{ nC}$)
- High Speed Switching with Low Capacitance ($C_{OSS} = 268\text{ pF}$)
- 100% Avalanche Tested
- This Device is Halide Free and RoHS Compliant with Exemption 7a, Pb-Free 2LI (on second level interconnection)

Applications

- SMPS, Solar Inverters, UPS, Energy Storage, EV Charging Infrastructure


MAXIMUM RATINGS ($T_J = 25\text{ }^\circ\text{C}$ unless otherwise noted)

Parameter		Symbol	Value	Unit
Drain-to-Source Voltage		V _{DSS}	650	V
Gate-to-Source Voltage		V _{GS}	-10/+22.6	V
Continuous Drain Current	T _C = 25 °C	I _D	142	A
Power Dissipation		P _D	576	W
Continuous Drain Current	T _C = 100 °C	I _D	101	A
Power Dissipation		P _D	288	W
Pulsed Drain Current (Note 1)	T _C = 25 °C t _p = 100 μs	I _{DM}	302	A
Continuous Source-Drain Current (Body Diode)	T _C = 25 °C V _{GS} = -3 V	I _S	90	
	T _C = 100 °C V _{GS} = -3 V		51	
Pulsed Source-Drain Current (Body Diode) (Note 1)	T _C = 25 °C V _{GS} = -3 V t _p = 100 μs	I _{SM}	335	
Single Pulse Avalanche Energy (I _{LPK} = 63 A, L = 0.1 mH) (Note 2)		E _{AS}	199	mJ
Operating Junction and Storage Temperature Range		T _J , T _{stg}	-55 to +175	°C
Lead Temperature for Soldering Purposes (1/8" from Case for 10 Seconds)		T _L	260	°C


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Single pulse, limited by max junction temperature.
2. E_{AS} of 199 mJ is based on starting $T_J = 25\text{ }^\circ\text{C}$, $L = 0.1\text{ mH}$, $I_{AS} = 63\text{ A}$, $V_{DD} = 100\text{ V}$, $V_{GS} = 18\text{ V}$.

$V_{(BR)DSS}$	$R_{DS(ON)}\text{ TYP}$	$I_D\text{ MAX}$
650 V	12 m Ω @ 18 V	142 A




N-Channel MOSFET



H-PSOF8L
CASE 100DC

MARKING DIAGRAM



A	= Assembly Location
Y	= Year
WW	= Work Week
ZZ	= Assembly Lot Code
BL012N065M3S	= Specific Device Code

ORDERING INFORMATION

Device	Package	Shipping [†]
NTBL012N065M3S	H-PSOF8L	2000 / Tape & Reel

[†] For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, [BRD8011/D](#).

THERMAL CHARACTERISTICS

Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case (Note 3)	$R_{\theta JC}$	0.26	°C/W

3. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted

RECOMMENDED OPERATING CONDITIONS

Parameter	Symbol	Value	Unit
Operation Values of Gate-to-Source Voltage	V_{GSop}	-3/+18	V

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

ELECTRICAL CHARACTERISTICS ($T_J = 25\text{ °C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
-----------	--------	-----------------	-----	-----	-----	------

OFF CHARACTERISTICS

Drain-to-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS} = 0\text{ V}$, $I_D = 1\text{ mA}$, $T_J = 25\text{ °C}$	650	–	–	V
Drain-to-Source Breakdown Voltage Temperature Coefficient	$\Delta V_{(BR)DSS} / \Delta T_J$	$I_D = 1\text{ mA}$, Referenced to 25 °C (Note 5)	–	86	–	mV/°C
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = 650\text{ V}$, $T_J = 25\text{ °C}$	–	–	10	μA
		$V_{DS} = 650\text{ V}$, $T_J = 175\text{ °C}$ (Note 5)	–	–	500	
Gate-to-Source Leakage Current	I_{GSS}	$V_{GS} = -10$, $V_{DS} = 0\text{ V}$	-1.0	–	–	μA
		$V_{GS} = +22.6\text{ V}$, $V_{DS} = 0\text{ V}$	–	–	+1.0	

ON CHARACTERISTICS

Drain-to-Source On Resistance	$R_{DS(ON)}$	$V_{GS} = 18\text{ V}$, $I_D = 40\text{ A}$, $T_J = 25\text{ °C}$	–	12	16.8	mΩ
		$V_{GS} = 18\text{ V}$, $I_D = 40\text{ A}$, $T_J = 175\text{ °C}$ (Note 5)	–	18	–	
		$V_{GS} = 15\text{ V}$, $I_D = 40\text{ A}$, $T_J = 25\text{ °C}$	–	15	–	
		$V_{GS} = 15\text{ V}$, $I_D = 40\text{ A}$, $T_J = 175\text{ °C}$ (Note 5)	–	20	–	
Gate Threshold Voltage	$V_{GS(TH)}$	$V_{GS} = V_{DS}$, $I_D = 20\text{ mA}$, $T_J = 25\text{ °C}$	2.0	2.7	4.0	V
Forward Transconductance	g_{FS}	$V_{DS} = 10\text{ V}$, $I_D = 40\text{ A}$ (Note 5)	–	38	–	S

CHARGES, CAPACITANCES & GATE RESISTANCE

Input Capacitance	C_{ISS}	$V_{DS} = 400\text{ V}$, $V_{GS} = 0\text{ V}$, $f = 1\text{ MHz}$ (Note 5)	–	3217	–	pF
Output Capacitance	C_{OSS}		–	268	–	
Reverse Transfer Capacitance	C_{RSS}		–	22	–	
Total Gate Charge	$Q_{G(TOT)}$	$V_{DD} = 400\text{ V}$, $I_D = 40\text{ A}$, $V_{GS} = -3/18\text{ V}$ (Note 5)	–	143	–	nC
Gate-to-Source Charge	Q_{GS}		–	34	–	
Gate-to-Drain Charge	Q_{GD}		–	33	–	
Gate Resistance	R_G	$f = 1\text{ MHz}$	–	1.7	–	Ω

SWITCHING CHARACTERISTICS

Turn-On Delay Time	$t_{d(ON)}$	$V_{GS} = -3/18\text{ V}$, $I_D = 40\text{ A}$, $V_{DD} = 400\text{ V}$, $R_G = 4.7\text{ Ω}$, $T_J = 25\text{ °C}$, $L_{stray} = 11\text{ nH}$ (Notes 4, 5)	–	17	–	ns
Turn-Off Delay Time	$t_{d(OFF)}$		–	50	–	
Rise Time	t_r		–	20	–	
Fall Time	t_f		–	12	–	
Turn-On Switching Loss	E_{ON}		–	203	–	μJ
Turn-Off Switching Loss	E_{OFF}		–	98	–	
Total Switching Loss	E_{TOT}		–	301	–	



ELECTRICAL CHARACTERISTICS ($T_J = 25\text{ }^{\circ}\text{C}$ unless otherwise specified) (continued)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
SWITCHING CHARACTERISTICS						
Turn-On Delay Time	$t_{d(ON)}$	$V_{GS} = -3/18\text{ V}$, $I_D = 40\text{ A}$, $V_{DD} = 400\text{ V}$, $R_G = 4.7\text{ }\Omega$, $T_J = 175\text{ }^{\circ}\text{C}$, $L_{stray} = 11\text{ nH}$ (Notes 4, 5)	–	13	–	ns
Turn-Off Delay Time	$t_{d(OFF)}$		–	60	–	
Rise Time	t_r		–	20	–	
Fall Time	t_f		–	13	–	
Turn-On Switching Loss	E_{ON}		–	220	–	μJ
Turn-Off Switching Loss	E_{OFF}		–	120	–	
Total Switching Loss	E_{TOT}		–	340	–	

SOURCE-TO-DRAIN DIODE CHARACTERISTICS

Forward Diode Voltage	V_{SD}	$I_{SD} = 40\text{ A}$, $V_{GS} = -3\text{ V}$, $T_J = 25\text{ }^{\circ}\text{C}$	–	4.5	6.0	V
		$I_{SD} = 40\text{ A}$, $V_{GS} = -3\text{ V}$, $T_J = 175\text{ }^{\circ}\text{C}$ (Note 5)	–	4.2	–	
Reverse Recovery Time	t_{RR}	$V_{GS} = -3\text{ V}$, $I_S = 40\text{ A}$, $di/dt = 1000\text{ A}/\mu\text{s}$, $V_{DS} = 400\text{ V}$, $T_J = 25\text{ }^{\circ}\text{C}$ (Note 5)	–	23	–	ns
Charge Time	t_a		–	14	–	
Discharge Time	t_b		–	9.1	–	
Reverse Recovery Charge	Q_{RR}		–	157	–	nC
Reverse Recovery Energy	E_{REC}		–	9.8	–	μJ
Peak Reverse Recovery Current	I_{RRM}		–	12	–	A

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. E_{ON}/E_{OFF} result is with body diode.

5. Defined by design, not subject to production test.



TYPICAL CHARACTERISTICS




Figure 1. Output Characteristics




Figure 2. Output Characteristics




Figure 3. Output Characteristics




Figure 4. Transfer Characteristics




Figure 5. On-Resistance vs. Gate Voltage




Figure 6. On-Resistance vs. Drain Current

TYPICAL CHARACTERISTICS




Figure 7. On-Resistance vs. Drain Current




Figure 8. On-Resistance vs. Junction Temperature




Figure 9. Gate Charge Characteristics




Figure 10. Capacitance Characteristics




Figure 11. Stored Energy vs. Drain to Source Voltage




Figure 12. Reverse Conduction Characteristics

TYPICAL CHARACTERISTICS




Figure 13. Reverse Conduction Characteristics




Figure 14. Maximum Power Dissipation vs. Case Temperature




Figure 15. Safe Operating Area




Figure 16. Avalanche Current vs. Pulse Time (UIS)




Figure 17. Inductive Switching Loss vs. Drain Current




Figure 18. Inductive Switching Loss vs. Drain Current

TYPICAL CHARACTERISTICS




Figure 19. Inductive Switching Loss vs. Gate Resistance




Figure 20. Inductive Switching Loss vs. Gate Resistance




Figure 21. Inductive Switching Loss vs. Gate Resistance




Figure 22. Inductive Switching Loss vs. Gate Resistance




Figure 23. Inductive Switching Loss vs. Drain Voltage




Figure 24. Inductive Switching Loss vs. Junction Temperature

TYPICAL CHARACTERISTICS





Figure 25. Transient Thermal Response

NTBL012N065M3S







REVISION HISTORY

Revision	Description of Changes	Date
0	Initial document release.	1/21/2026




H-PSOF8L 9.90x10.38x2.30, 1.20P
CASE 100DC
ISSUE D

DATE 30 JUL 2024


GENERIC MARKING DIAGRAM*


XXXX = Specific Device Code
A = Assembly Location
Y = Year
WW = Work Week
ZZ = Assembly Lot Code

NOTES:

1. PACKAGE STANDARD REFERENCE: JEDEC MO-299, ISSUE B.
2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2018.
3. "e" REPRESENTS THE TERMINAL PITCH.
4. THIS DIMENSION INCLUDES ENCAPSULATION THICKNESS "A1", AND PACKAGE BODY THICKNESS, BUT DOES NOT INCLUDE ATTACHED FEATURES, e.g., EXTERNAL OR CHIP CAPACITORS. AN INTEGRAL HEATSLUG IS NOT CONSIDERED AS ATTACHED FEATURE.
5. A VISUAL INDEX FEATURE MUST BE LOCATED WITHIN THE HATCHED AREA.
6. DIMENSIONS b1, L1, L2 APPLY TO PLATED TERMINALS.
7. THE LOCATION AND SIZE OF EJECTOR MARKS ARE OPTIONAL.
8. THE LOCATION AND NUMBER OF FUSED LEADS ARE OPTIONAL.

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	2.20	2.30	2.40
A1	1.70	1.80	1.90
b	0.70	0.80	0.90
b1	9.70	9.80	9.90
b2	0.35	0.45	0.55
c	0.40	0.50	0.60
D	10.28	10.38	10.48
D/2	5.09	5.19	5.29
D1	10.98	11.08	11.18
D2	3.20	3.30	3.40
D3	2.60	2.70	2.80
D4	4.45	4.55	4.65
D5	3.20	3.30	3.40
D6	0.55	0.65	0.75
E	9.80	9.90	10.00
E1	7.30	7.40	7.50
E2	0.30	0.40	0.50
E3	7.40	7.50	7.60
E4	8.20	8.30	8.40

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
E5	9.36	9.46	9.56
E6	1.10	1.20	1.30
E7	0.15	0.18	0.21
e	1.20 BSC		
e/2	0.60 BSC		
H	11.58	11.68	11.78
H/2	5.74	5.84	5.94
H1	7.15 BSC		
L	1.63	1.73	1.83
L1	0.60	0.70	0.80
L2	0.50	0.60	0.70
L3	0.43	0.53	0.63
Θ	10° REF		
Θ1	10° REF		
aaa	0.20		
bbb	0.25		
ccc	0.20		
ddd	0.20		
eee	0.10		

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	98AON80466G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	H-PSOF8L 9.90x10.38x2.30, 1.20P	PAGE 1 OF 1

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales

