molex



Part Number : 797580011
Product Description : Pre-Crimped Lead SL Female-to-SL Female, Tin (Sn) Plating, 300.00mm Length, 22 AWG, Black
Series Number : 79758
Status : Obsolete
Product Category : Power and Signal Cable Assemblies

Obsolete

Documents and Resources

Drawings

797580011_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Power and Signal Cable Assemblies
Series	79758
Description	Pre-Crimped Lead SL Female-to-SL Female, Tin (Sn) Plating, 300.00mm Length, 22 AWG, Black
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	SL Crimp Terminals
Keyword	Pre-Crimped Leads
Product Name	SL
UPC	884982052758

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.480/g
Packaging Type	Bag
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Size (AWG)	22

Obsolete

Downloaded from Arrow.com.

Mates With / Use With

Use with Part(s)

Description	Part Number
SL Single Row Crimp Housings and CPA Retainers	70066
SL Dual Row Crimp Housings	70450

This document was generated on Apr 14, 2026

Obsolete

Downloaded from Arrow.com.