



Part Number : [467650301](#)

Product Description : 0.40mm Pitch Micro HDMI Connector, Right-Angle Receptacle, Surface Mount, with Pick-and-Place Polyimide Tape, 19 Circuits, Lead-Free

Series Number : 46765

Status : Active

Product Category : I/O Connectors



Documents and Resources

Drawings

[467650301_sd.pdf](#)

[PK-46765-001-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


[EE-46765-001-001.pdf](#)

Specifications

[PS-46765-003-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	I/O Connectors
Series	46765
Description	0.40mm Pitch Micro HDMI Connector, Right-Angle Receptacle, Surface Mount, with Pick-and-Place Polyimide Tape, 19 Circuits, Lead-Free
Application	Wire-to-Board
Component Type	Receptacle
Product Name	Micro HDMI
Standard	HDMI 1.4
Type	D
UPC	884982716131

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	0.8A
-------------------------------	------

Grounding to Panel	Yes
Shielded	Yes
Shield Type	Full Shield
Voltage - Maximum	30V

Physical

Boot Color	N/A
Circuits (Loaded)	19
Circuits (maximum)	19
Flammability	94V-0
Gender	Female
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Mounting Style	Bottom-Mount
Net Weight	0.333/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Panel Mount	No
PCB Retention	Yes
Pitch - Mating Interface	0.40mm
Pitch - Termination Interface	0.40mm
Plating min - Mating	0.381µm
Plating min - Termination	0.051µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Termination Interface Style	Surface Mount
Waterproof / Dustproof	No

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	2
Max-Temp	260

This document was generated on Jun 02, 2026