

Product data sheet

Specifications



APC IT Power Distribution Module 2 Pole 3 Wire 30A L3-L1 L6-30 500CM

PDM2330L6-31-500

Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead time	Usually Ships within 3 Weeks

Main

Main Input Voltage	208 V
Main Output Voltage	208 V
Provided equipment	Installation guide

Physical

Colour	Black
Height	12.7 cm
Width	44.4 cm
Depth	40.6 cm
Net weight	4.29 kg

Input

Network frequency	60 Hz
Max line current	30 A

Output

Max current draw	30 A
Number of power socket outlets	1 NEMA L6-30R

Conformance

Product certifications	UL listed
-------------------------------	-----------

Environmental

Ambient air temperature for operation	0...30 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...40 °C
Storage Relative Humidity	0...95 %

Storage altitude	0...4572 m
------------------	------------

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
------------------------------	---

Package 1 Height	12.7 cm
------------------	---------

Package 1 Width	40.6 cm
-----------------	---------

Package 1 Length	44.4 cm
------------------	---------

Package 1 Weight	5.2 kg
------------------	--------

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

[Environmental Disclosure](#)

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

No

[EU RoHS Directive](#)

Compliant with Exemptions

Use Again

Repack and remanufacture

End of life manual availability

[End of Life Information](#)

Take-back

Yes

WEEE Label


 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

