





PART NUMBER SEE SHEET 2



spec ref *				dr		Rainbow Zhan	2015/07/07		projection		MM		size		A3		scale		3:2						
tolerance std				eng		Rainbow Zhan		2015/08/18						ecn no		ELX-DG-21665-1									
ASME Y14.5				chr		Fancy Zhang		2015/08/18																	
				appr		Pei-Ming Zheng		2015/08/18		product family				PwrBlade+				rel level		Released					
surface		linear		0.X		±0.5				title		2ACP + 28S + 4LP + 8ACP				dwg no		10106266-A407001				rev		B	
				0.XX		±0.25																			
				0.XXX		±0.10																			
ASME Y14.5		angular		0°		±2°		www.fci.com		cat. no.		Product - Customer Drw				sheet 1 of 3									



Copyright FCI.

A

B

C

D

PRODUCT NO.	ROWS	HIGH POWER SIGNAL							LP				HIGH POWER																				
		E1	P1	P2	1	2	3	4	5	6	7	P3	P4	P5	P6	P7	P8	P9	P10	P11	P12	P13	P14	E2									
10106266-A407001LF	DCBA																																


CODE	DESCRIPTION
E	STD SIGNAL CONTACT
HI	STD HIGH POWER CONTACT
HA	METAL HOLD DOWN
LJ	STD LOW POWER CONTACT

A

B

C

D



dr	Rainbow Zhan	2015/07/07	projection	MM	size	A3	scale	3:2				
eng	Rainbow Zhan	2015/08/18			ecn no	ELX-DG-21665-1						
chr	Fancy Zhang	2015/08/18										
appr	Pei-Ming Zheng	2015/08/18	product family		PwrBlade+		rel level	Released				
			title		2ACP + 28S + 4LP + 8ACP		dwg no		10106266-A407001	rev	B	
			VERTICAL STB HEADER									
www.fci.com			cat. no.		Product - Customer Drw				sheet 2 of 3			

A

B

C

D

A

B

C

D

NOTES:

1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE MARK CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.

2) MATERIALS:
-HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
-SIGNAL CONTACT - COPPER ALLOY.
-POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.

3) PLATING SPECIFICATION :10116351


4) DENOTES CONNECTOR KEEP OUT ZONE.

5) DATUM AND BASIC DIMENIONS ARE ESTABLISHED BY CUSTOMER.

6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.

7) 1.15±0.025MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02±0.07MM HOLE.

8) PRODUCT SPECIFICATION : GS-12-658.
APPLICATION SPECIFICATION : GS-20-141.
PRODUCT PACKAGE SPECIFICATION : GS-14-1502.



dr	Rainbow Zhan	2015/07/07	projection	MM	size	A3	scale	3:2			
eng	Rainbow Zhan	2015/08/18			ecn no	ELX-DG-21665-1					
chr	Fancy Zhang	2015/08/18									
appr	Pei-Ming Zheng	2015/08/18	product family		PwrBlade+	rel level			Released		
			title		2ACP + 28S + 4LP + 8ACP		dwg no		10106266-A407001	rev	B
VERTICAL STB HEADER											
www.fci.com			cat. no.		Product - Customer Drw				sheet 3 of 3		