© 2026 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	23JUN2026	SB	AR

ELECTRICAL CHARACTERISTICS:


IMPEDANCE : 50Ω
VOLTAGE RATING : 60 V(rms)
FREQUENCY RANGE : DC~ 6 GHz
DIELECTRIC WITHSTANDING VOLTAGE : >200 V
INSULATION RESISTANCE : >1000 MΩ
VSWR : <1.50
3RD INTERMODULATION : N/A


MATERIAL AND FINISH:


SMA:
BODY, NUT AND WASHER: BRASS HBi59-1
GOLD 3μ"/NICKEL 100μ"/COPPER 50μ"
CONTACT: BERYLLIUM COPPER C17200
GOLD 3μ"/NICKEL 100μ"/COPPER 50μ"
INSULATOR : PTFE MIL-P-19468
GASKET: SILICONE
COLOR RED
HEAT SHRINK: PO, BLACK


UMCC GEN1:
CENTER CONTACT: PHOSPHOR BRONZE
GOLD 3.9μ"/NICKEL 39μ"
GROUND CONTACT: PHOSPHOR BRONZE
GOLD 1.9μ"/NICKEL 39μ"
HOUSING: PBT
UL94V-0

CABLE: ⌀1.13MM BLACK











RECOMMENDED MOUNTING HOLE
PANEL THICKNESS : 3.4MM MAX



NUT



WASHER

PART NUMBER	LENGTH "L" (mm)	INSERTION LOSS
2556949-1	101.6 +6/-0	<1.17 dB @ 6GHz
2556949-2	152.4 +6/-0	<1.50 dB @ 6GHz
2556949-3	203.2 +8/-0	<1.84 dB @ 6GHz
2556949-4	254.0 +8/-0	<2.18 dB @ 6GHz
2556949-5	304.8 +8/-0	<2.52 dB @ 6GHz

MECHANICAL CHARACTERISTICS		
CABLE RETENTION FORCE		≥15 N
CABLE STATIC BENDING RADIUS		4.5 mm MIN.
DURABILITY	≥500cycles(SMA)	≥30cycles(UMCC)

ENVIRONMENTAL PARAMETER	
TEMPERATURE RANGE	-40℃ ~+80℃
PROTECTION GRADE	IP68(UNMATED)
CORROSION	MIL-STD 202,Meth.101,Cond.B
ROHS	COMPLIANT.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± 0.3
2 PLC ± 0.2
3 PLC ± 0.1
4 PLC ± –
ANGLES ± –

MATERIAL: SEE NOTE
FINISH: SEE NOTE

DWN SUGEESH B 30MAR2026
CHK ANSON M 12JUN2026
APVD ARAVINDHAN R 23JUN2026
PRODUCT SPEC 108-162630
APPLICATION SPEC —
WEIGHT 0

TE Connectivity

NAME
RP-SMA JACK BH STR TO
UMCC GEN1 PLUG R/A, 1.13MM CABLE
—

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2556949	—


CUSTOMER DRAWING | SCALE NTS | SHEET 1 OF 2 | REV A

1470-19 (1/15)

Downloaded from Arrow.com.

© 2026 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	–	SEE SHEET 1	–	—	—



ASSEMBLY





NUT




WASHER

NOTE:
1. 1 PCS / BAG
2. 50 BAG / BOX (50 PCS / BOX)
3. 10 BOX / CARTON (500 PCS / CARTON)
4. SINGLE WEIGHT:
   2556949–1 : 6.02g
   2556949–2 : 6.52g
   2556949–3 : 7.03g
   2556949–4 : 7.54g
   2556949–5 : 8.05g
5. WEIGHT PER BOX:
   2556949–1 : 5360g
   2556949–2 : 5610g
   2556949–3 : 5865g
   2556949–4 : 6120g
   2556949–5 : 6375g





10 BOX



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± –
1 PLC	± 0.3
2 PLC	± 0.2
3 PLC	± 0.1
4 PLC	± –
ANGLES	± –

MATERIAL: SEE NOTE

FINISH: SEE NOTE

DWN	SUGEESH B 30MAR2026
CHK	ANSON M 12JUN2026
APVD	ARAVINDHAN R 15JUN2026
PRODUCT SPEC	108–162630
APPLICATION SPEC	—
WEIGHT	0

TE Connectivity

NAME: RP–SMA JACK BH STR TO UMCC GEN1 PLUG R/A, 1.13MM CABLE –

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C–2556949	—

CUSTOMER DRAWING

SCALE	SHEET	REV
NTS	2 OF 2	A

Downloaded from Arrow.com.