638865-1 ✔ ACTIVE

AMP | Timer Connector System

TE Internal #: 638865-1

Single Wire Seal (SWS), Brown, Silicone, 2.8 – 3.2 mm [.11 – .126 in] Insulation Diameter, Timer Connector System

View on TE.com >

Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Single Wire Seal (SWS)**

Primary Product Color: **Brown**

Primary Product Material: **Silicone**

Compatible Insulation Diameter Range: **2.8 – 3.2 mm [.11 – .126 in]**

Shore A Hardness: **40**

Features

Product Type Features

Connector Seal & Plug Type	Single Wire Seal (SWS)

Body Features

Primary Product Color	Brown
Primary Product Material	Silicone

Dimensions

Compatible Insulation Diameter Range	2.8 – 3.2 mm[.11 – .126 in]

Packaging Features

Packaging Method	Package
Packaging Quantity	50000

Other

Shore A Hardness	40

Product Compliance

For compliance documentation, visit the product page on TE.com>


Downloaded from Arrow.com.

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 1355881-3
MQS GRIFFSCHALE 6P

TE Part # 1743632-2
HYB SLD 36P PLUG ASSY




TE Part # 1-1719504-1
TAB 2.8x0.8 CONTACT CS SWS Sn



TE Part # 2188967-3
SINGLE WIRE SEAL FOR 6.3MM

Also in the Series | Timer Connector System

Downloaded from Arrow.com.



Automotive Connector Locks & Position Assurance(15)




Automotive Housings(187)




Automotive Signal & Power Connector Housings(137)



Connector Seals & Cavity Plugs(33)




Crimp Terminal Housings(13)



Other Automotive Connector Accessories(1)

Customers Also Bought



TE Part #HDC9-JDL082397
DUST CAP, 9P, REC, BLK, LANYARD, HD10



TE Part #EK5194-000
ES2000-NO.6-H2-0-39MM



TE Part #DTM04-2P-EP10
REC, 2P, BLK, 120 OHM RESISTOR, AU, B



TE Part #DT06-4S-LC01
PLG, 4P, BLK, E, SEAL RET,DIN BKSHL ADPT



TE Part #1-66358-3
III+ SKT,18-14,30AU/FL,STRIP



TE Part #1-66740-1
TYPE XII FEMALE CONT (STRIP)



TE Part #1-480707-2
09P UMNL CAP HSG RED



TE Part #1-968857-1
AMP MCP 2.8, CONTACT SWS



TE Part #1394511-1
EINZELLEITDICHTG,WS



TE Part #1-968874-1
AMP MCP 2.8, CONTACT (LP)

Documents

Downloaded from Arrow.com.

Product Drawings

CABLE SEAL 12 AWG PWR TMR TERM

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_638865-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_638865-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_638865-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Specifications

Application Specification

English

Downloaded from Arrow.com.