



PRODUCT NUMBER

PITCH

VLxx32x000J0G

3.81 mm

RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material:

- Item③Pin: Copper Tin plated
 - Item⑤Terminal(housing): Thermoplastic (UL94 V-0)
 - Item⑥With flange nut: Brass ,M2.5
 - Item④Terminal(cover): Thermoplastic (UL94 V-0)
- Electrical: cULus
- Voltage rating: 300V
 - Current rating: 10A
 - Withstanding Voltage: 1.6 KV
 - Operating temperature: -40°C to +115°C
 - Soldering temperature: 260°C±5°C/5 Sec
 - Safety Approval: cULus

N=Number of poles
 Dim L=(N/2-1)×3.81+14.2
 Dim B=(N/2-1)×3.81
 Dim C=(N/2-1)×3.81+9.0

Poles	Tolerance
2x2-2x6p	±0.15
2x7-2x12p	±0.25
2x13-2x18p	±0.35
2x19-2x24p	±0.40

PART NO.: VL xx 3 2 x 0 00J0 G

		Color	RoHS compliant
Solid block	0	Black (RAL9005)	(lead<4%)
No. of poles	2	Red (RAL3001/D)	In copper Alloy
04 2x2poles	3	Orange(RAL2011/P)	
06 2x3poles	4	Yellow(RAL1018/A)	
...	5	Green(RAL6018/T)	
48 2x24poles	6	Blue (RAL5015/A)	
	8	Grey(RAL7035/D)	
	9	White(RAL1102)	
	C	Green(RAL6018/U)	

mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK									
ltr ecn no dr date				tolerances unless otherwise specified						title TERMINAL BLOCK									
				angles		linear		MM		PLUGGABLE SOCKET, WITH FLANGE, VERTICAL									
						X.±0.5													
						X.X±0.3													
				X°±1°		X.XX±0.1		scale											
				dr		EVIN ZHONG		042814											
				enr		EVIN ZHONG		042814											
				chr		HANKE FENG		042814											
				appd		SHI JUN		042814		dwg no VLxx32x000J0G									
										sheet 1 of 1 size A4									
sheet index		revision sheet		A 1						type CUSTOMER Drawing									