

Part Number : [1716920106](#)

Product Description : Mega-Fit Receptacle Housing,
Dual Row, 6 Circuit, UL 94 V-0, Bag

Series Number : 171692

Status : Active

Product Category : Connector Housings



Documents and Resources

Drawings

[1716920106_sd.pdf](#)

[PK-170001-001-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[AS-76823-100-001.pdf](#)


[PS-76823-100-001.pdf](#)

[TS-170001-001-001.pdf](#)

[TS-76823-100-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	171692
Description	Mega-Fit Receptacle Housing, Dual Row, 6 Circuit, UL 94 V-0, Bag
Application	Power, Wire-to-Board, Wire-to- Wire
Product Name	Mega-Fit
UPC	887191246864

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	6
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No

Lock to Mating Part	Yes
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	3.377/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.70mm
Pitch - Termination Interface	5.70mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +120°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mega-Fit Right-Angle, Dual Row, Through Hole Headers	<u>172064</u>
Mega-Fit Vertical, Dual Row Through Hole Headers	<u>172065</u>
Mega-Fit Right-Angle Dual Row Headers	<u>76825</u>
Mega-Fit and Mega-Fit Slim Vertical Dual Row Headers	<u>76829</u>

Use with Part(s)

Description	Part Number
Mega-Fit Crimp Terminal, Female, Tin (Sn) Plating, 16-14 AWG, Reel	<u>768230321</u>
Mega-Fit Crimp Terminal, Female, Tin (Sn) Plating, 12 AWG, Reel	<u>768230322</u>
Mega-Fit Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 16-14 AWG, Reel	<u>1720630311</u>
Mega-Fit Crimp Terminal, Female,	<u>1720630312</u>

0.38µm Gold (Au) Plating, 12 AWG, Reel	
Mega-Fit Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 16-14 AWG, Reel	<u>1720631311</u>
Mega-Fit Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 12 AWG, Reel	<u>1720631312</u>
Pre-Crimped Lead Mega-Fit Female-to-Mega-Fit Female, Gold (Au) Plating, 150.00mm Length, 16 AWG, Black	<u>797582037</u>
Pre-Crimped Lead Mega-Fit Female-to-Mega-Fit Female, Gold (Au) Plating, 300.00mm Length, 16 AWG, Black	<u>797582038</u>
Pre-Crimped Lead Mega-Fit Female-to-Mega-Fit Female, Gold (Au) Plating, 150.00mm Length, 12 AWG, Black	<u>797582039</u>
Pre-Crimped Lead Mega-Fit Female-to-Mega-Fit Female, Gold (Au) Plating, 300.00mm Length, 12 AWG, Black	<u>797582040</u>

This document was generated on May 19, 2026