

Part Number : [936000212](#)

Product Description : Heavy-Duty EMC - Electromagnetic Compatibility Metal Cable Gland with Gasket, for 15.00-20.00mm Cable, M32x1.5 Thread

Series Number : 93600

Status : Active

Product Category : Heavy-Duty Cable Glands


Engineering Part Number : 7000.7336.0



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Cable Glands
Series	93600
Description	Heavy-Duty EMC - Electromagnetic Compatibility Metal Cable Gland with Gasket, for 15.00-20.00mm Cable, M32x1.5 Thread
Cable Gland Type	IP68 - EMC
IP Rating	IP68
Product Name	Heavy-Duty Connectors
Standard	EN 50262
UPC	887191842448

Physical

Cable Diameter	15.00-20.00mm
Material - Cable Gland	Brass
Material - Gasket	Elastomer
Material - Plating	Nickel
Net Weight	117.000/g
Packaging Type	Bag
Temperature Range - Operating	-40° to +125°C
Thread Size	M32x1.5
Thread Type	(M) Metric

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Where Electromagnetic

	Compatibility is required, industrial connectors, hoods, housings, sealed enclosures, and boxes
--	---

This document was generated on Jun 16, 2026