


**Part Number :** 908160008
**Product Description :** Picoflex Surface Mount Latched Vertical Header with PCB Pegs, 8 Circuits, Tin (Sn) Plating, Black
**Series Number :** 90816
**Status :** Active
**Product Category :** PCB Headers and Receptacles

## Documents and Resources

### Drawings

908160008_sd.pdf

PK-90816-006-001.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

### Specifications

908140000-AS-000.pdf

PK-90816-001-001.pdf

PS-99020-0011-001.pdf

TS-90816-001-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Compliant with Exemption 44; 33 |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | PCB Headers and Receptacles |
| Series | 90816 |
| Description | Picoflex Surface Mount Latched Vertical Header with PCB Pegs, 8 Circuits, Tin (Sn) Plating, Black |
| Application | Wire-to-Board |
| Component Type | PCB Header |
| Product Name | Picoflex |
| UPC | 883906498825 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 1.2A |
| Voltage - Maximum | 250V |

### Physical

| | |
|---|---|
| Breakaway | No |
| Circuits (Loaded) | 8 |
| Circuits (maximum) | 8 |
| Color - Resin | Black |
| Durability (mating cycles max) | 5 |

Downloaded from Arrow.com.

| | |
|---|---|
| First Mate / Last Break | No |
| Gender | Male |
| Glow-Wire Capable | No |
| Guide to Mating Part | No |
| Keying to Mating Part | N/A |
| Lock to Mating Part | Yes |
| Material - Metal | Brass |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Nickel |
| Material - Resin | Nylon |
| Net Weight | 0.392/g |
| Number of Rows | 1 |
| Orientation | Vertical |
| Packaging Type | Tube |
| PCB Locator | Yes |
| PCB Retention | No |
| PCB Thickness - Recommended | 1.60mm |
| PC Tail Length | 1.05mm |
| Pitch - Mating Interface | 1.27mm |
| Pitch - Termination Interface | 1.27mm |
| Plating min - Mating | 0.076µm |
| Plating min - Termination | 3.000µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Shrouded | Partially Shrouded |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |
| Termination Interface Style | Surface Mount |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| Picoflex PF-50 Low Profile IDT Receptacles | 90327 |

Downloaded from Arrow.com.

Downloaded from Arrow.com.