

ZBF 12:UNBEDRUCKT - Zack Marker strip, flat



0809735

<https://www.phoenixcontact.com/us/products/0809735>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack Marker strip, flat, Strip, white, unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 12 mm, Number of individual labels: 5, text field height: 12.15 mm, text field width: 5.15 mm

Your advantages

- Unmarked marking strips can be custom-labeled with a plotter or by hand
- Other pitches available on request
- The ZBF zack marker strip system with flat marker groove is a marking solution for modular terminal blocks and electronics modules
- The multi-section marking strips are easy to fit and can be easily separated if required

Commercial data

Item number	0809735
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2112
GTIN	4017918591694
Weight per piece (including packing)	0.59 g
Weight per piece (excluding packing)	0.59 g
Customs tariff number	39269097
Country of origin	DE

ZBF 12:UNBEDRUCKT - Zack Marker strip, flat



0809735

<https://www.phoenixcontact.com/us/products/0809735>

Technical data

Product properties

Product type	Terminal marking
Pitch	12 mm
Type	flat

Marking

Number of individual labels	5
Number of individual labels per row	5
Number of marker strips	10

Dimensions

Width	12 mm
Pitch	12 mm

Text field

Text field width	5.15 mm
Text field height	12.15 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations


Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	latching
---------------	----------

Drawings

Schematic diagram



ZBF 12:UNBEDRUCKT - Zack Marker strip, flat



0809735

<https://www.phoenixcontact.com/us/products/0809735>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZBF 12:UNBEDRUCKT - Zack Marker strip, flat



0809735

<https://www.phoenixcontact.com/us/products/0809735>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.005 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com