




CGPT-76/38-0-SP Product Details

Share

Print

Email



CGPT-76/38-0-SP

TE Internal Number: 5067104003

Active

Heat Shrink Tubing

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Heat Shrinkable Tubing
- Product Name = CGPT
- Product Source = U.K.
- Flexible
- Thin Wall Style

[View all Features](#)

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Heat Shrinkable Tubing
- Color = Black

Dimensions:

- Expanded ID, Min. (mm [in]) = 76.00 [2.992]
- Recovered ID, Max. (mm [in]) = 38.00 [1.496]

Body Features:

- Product Name = CGPT
- Pliancy = Flexible
- Wall Style = Thin
- Wall Type = Single
- Material = Crosslinked Polyolefin
- Shrink Ratio = 2:1
- Fluid Type = Brake Fluid, Chemicals/Solvents, Water
- Resistant To = Fluids, Mechanical Damage, Strain
- Wall Thickness - Full Recovery (Nominal) (mm [in]) = 1.27 [0.050]

Housing Features:

- Material Systems = No

Industry Standards:

- Government/Industry Qualification = No
- Flammability Rating Type = Flame-Retardant
- UL Rating = Recognized
- CSA Certified = Yes
- Approved Standards = CSA LR31929, UL E35586
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Environmental:

- Fluid Resistance = Splash Protection
- Operating Temperature (°C) = -40 - +135

Conditions for Usage:

- Full Recovery Temperature (°C) = 120
- Shrink Temperature, Min. (°C) = 80
- High Temperature Compatible = No

Operation/Application:

- Application = Cable Bundling, Cable Jacketing, Color Coding, Identification, Insulation and Protection
- Emission Free = No
- Product Use = Cables, Electronic Components, Pipes, Wires

Packaging Features:

- Packaging Method = Spool

Product Availability:

- Product Source = U.K.

Other:

- Brand = Raychem

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

