

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



COPYRIGHT --

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	3	modify the packaging specific	03AUG2018	E.Z	W.H

NOTES:

1. MATERIAL:

1.1 HOUSING : HIGH TEMPERATURE THERMOPLASTIC
UL94V-0, COLOR: NATURAL.1.2 ACTUATOR: HIGH TEMPERATURE THERMOPLASTIC
UL94V-HB, COLOR: BLACK.

1.3 CONTACT: COPPER ALLOY.

1.4 FITTING NAIL : COPPER ALLOY.

2. FINISH:

2.1 CONTACT: GOLD PLATING 3u" MIN. ON CONTACT AREA.
GOLD PLATING 1u" MIN. ON SOLDER TAILS.
50u"MIN. NICKEL UNDERPLATING OVERALL.2.2 FITTING NAIL: TIN PLATING 80u" MIN. ON SOLDER TAILS.
50u" MIN. NICKEL UNDERPLATING OVERALL.

3. SPECIFICATION:

VOLTAGE: 30V AC/DC

CURRENT RATING: 0.5 AMPERE

CONTACT RESISTANCE: INITIAL 50 mOHMS MAX.

AFTER TEST Δ30 mOHMS MAX.

DIELECTRIC WITHSTANDING VOLTAGE: 250V AC/1 MINUTE;




INSULATION RESISTANCE: 500M OHMS MIN.

FFC/FPC WITHDRAWL FORCE: 0.20N PER CONTACT MIN;

FFC/FPC THICKNESS: 0.20+/-0.03mm.

4. THE PRODUCT IS RoHS AND HF COMPLIANT.

△ PIN NO.



45	13.8	14.5	13.85	13.2	12.6	15.0	4-2328724-5
39	12.0	12.7	12.05	11.4	10.8	13.2	3-2328724-9
33	10.2	10.9	10.25	9.6	9.0	11.4	3-2328724-3
31	9.6	10.3	9.65	9.0	8.4	10.8	3-2328724-1
25	7.8	8.5	7.85	7.2	6.6	9.0	2-2328724-5
21	6.6	7.3	6.65	6.0	5.4	7.8	2-2328724-1
15	4.8	5.5	4.85	4.2	3.6	6.0	1-2328724-5
13	4.2	4.9	4.25	3.6	3.0	5.4	1-2328724-3
PIN NO.	DIM.F	DIM.E	DIM.D	DIM.C	DIM.B	DIM.A	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN Eliana.Zhang 29DEC2017

CHK Wenke.He 29DEC2017

APVD Wenke.He 29DEC2017

PRODUCT SPEC

108-115143

APPLICATION SPEC

WEIGHT SEE TABLE

CUSTOMER DRAWING



TE Connectivity

FPC CONNECTOR PITCH=0.30mm

FRONT FLIP

NAME

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 - C-2328724

SCALE 10:1 SHEET 1 OF 3 REV 3


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



- NOTES: (APPLIED TO CURRENT SHEET)
1. THE DIRECTION OF EACH CONNECTOR ON A EMBOSS IS REFERRED TO THIS DRAWING.
 2. PACKAGED IN EMBOSS TAPE AND PLASTIC RELL 5000 PCS PER RELL.
 3. WINDING THE COVER TAPE AROUND THE OUTER PERIPHERY IN A TURN.






TABLE A

P/N	PIN NO.	Amount of packing				Weight of packing		
		DIM.A	DIM.B	Pcs/Reel	Reel/Carton	PCS/Carton	Unit weigh(g)	Net weight(kg)
1-2328724-3	13	7.50	16.00	5,000	7	35,000	0.0305	1.068
1-2328724-5	15			5,000	7	35,000	0.0345	1.208
2-2328724-1	21			5,000	7	35,000	0.0455	1.593
2-2328724-5	25			5,000	7	35,000	0.0550	1.925
3-2328724-1	31	11.50	24.00	5,000	5	25,000	0.0645	1.613
3-2328724-3	33			5,000	5	25,000	0.0665	1.663
3-2328724-9	39			5,000	5	25,000	0.0775	1.938
4-2328724-5	45			5,000	5	25,000	0.0885	2.213

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Eliana.Zhang 29DEC2017		TE Connectivity											
		CHK Wenke.He 29DEC2017													
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME FPC CONNECTOR PITCH=0.30mm FRONT FLIP —											
		0 PLC ± 0.4 1 PLC ± 0.25 2 PLC ± 0.15 3 PLC ± 0.10 4 PLC ± — ANGLES ± 3.0													
MATERIAL —		FINISH —		WEIGHT SEE TABLE		SIZE A3		CAGE CODE —		DRAWING NO C-2328724		RESTRICTED TO —			
CUSTOMER DRAWING										SCALE 10:1		SHEET 3 OF 3		REV 3	