

Part Number : 732161870

Product Description : TNC Jack, Straight, Bulkhead Receptacle, PCB, Through Hole, Die Cast Body, Nickel (Ni) Plated, Jam Nut and Lockwasher Included, 50 Ohms



Series Number : 73216

Status : Active

Product Category : RF / Coaxial Connectors

Documents & Resources

Drawings

732161870_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	ⓘ per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73216
Description	TNC Jack, Straight, Bulkhead Receptacle, PCB, Through Hole, Die Cast Body, Nickel (Ni) Plated, Jam Nut and Lockwasher Included, 50 Ohms
Application	RF
Product Name	TNC
Style	PCB
Type	Miniature
UPC	883906283773

Electrical

Frequency	11 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	22.774/g
Orientation	Straight
Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Bulkhead
PCB Mounting	Through Hole

PCB Thickness - Recommended	4.30mm
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Lead-Free Process Capability	WAVE
Max-Cycle	2
Max-Temp	245

This document was generated on Sep 17, 2025