



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		A	REVISED PER ECO-15-001494	05FEB2015	AP	DD




NOTCH DESIGNATES ROW A



1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.



2 FINISH:
30µ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.



192X Ø0.46±0.05
PLATED THRU HOLE

192X Ø0.55±0.013
DRILL HOLE
⌀0.10

UNGUIDED
BACKPLANE HOLE PATTERN
(CONNECTOR SIDE)




SECTION A-A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: KIRAN HOLAL 09JAN2013	TE Connectivity	
DIMENSIONS:		CHK: D.DIXON 09JAN2013		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD: D.DIXON 09JAN2013	NAME:	IMPACT, 4 PAIR, 16 COLUMN, HEADER
	0 PLC ±	PRODUCT SPEC	SIZE: CAGE CODE: DRAWING NO:	RESTRICTED TO:
	1 PLC ±0.25	APPLICATION SPEC		
	2 PLC ±0.13	WEIGHT: -	A100779C=2007832	SCALE: 6:1
	3 PLC ±	Customer Drawing		
MATERIAL:	ANGLES: -	Customer Drawing	Customer Drawing	SHEET 1 OF 2
FINISH: SEE TABLE		REV A		

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-

	5.5	2007832-3
	4.9	2007832-2
	4.5	2007832-1
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT			DWN KIRAN HOLAL	09JAN2013	 TE Connectivity		
DIMENSIONS:			CHK D.DIXON	09JAN2013			
mm			APVD D.DIXON	09JAN2013	NAME IMPACT, 4 PAIR, 16 COLUMN, HEADER UNGUIDED, OPEN END WALL SIGNAL MODULE, 0.46 PTH		
			TOLERANCES UNLESS OTHERWISE SPECIFIED:				
			0 PLC ± 1 PLC ±0.25 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ± FINISH				
MATERIAL			SEE TABLE		RESTRICTED TO		
-			-		-		
			Customer Drawing		SIZE A1	CAGE CODE 00779	DRAWING NO 2007832
					SCALE 5:1	SHEET 2	OF 2
					REV A		