

Products

Documentation

Resources

My Account

Customer Support

[Home](#) > [Products](#) > [By Type](#) > [Relays](#) > [Product Feature Selector](#) > Product Details

SCERX22ACA Product Details



SCERX22ACA

 [Active](#)

Time Delay Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- ? SCE Specification Grade True Off - Delay Timing Series
- ? Time Delay Relay
- ? Input Voltage = 120 VAC
- ? Input Voltage = 125 VDC
- ? Contact Arrangement = 2 Form C, DPDT, 2 C/O

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information	
Product Drawings: ? None Available Catalog Pages/Data Sheets: ? None Available Product Specifications: ? None Available Application Specifications: ? None Available Instruction Sheets: ? None Available CAD Files: ? None Available	Additional Information: ? Product Line Information Related Products: ? Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: ? Product Type = Time Delay Relay ? Termination Type = 8 -Pin Octal Style Plug Electrical Characteristics: ? Input Voltage (VAC) = 120 ? Input Voltage (VDC) = 125 ? Contact Rating = 5A Resistive @ 120/240 VAC Body Related Features: ? Series = SCE Specification Grade True Off - Delay Timing Contact Related Features: ? Mounting Options = Socket ? Mode of Operation = True Off -Delay ? Delay Time = 1 second to 30 seconds ? Type of Control = Knob ? Repeatability, Max. = ± 1% ? Approved Standards = CE Approved, CSA Certified, UL Recognized ? Approx. Dimensions (L x W x H) (mm [in]) = 50.00 x 50.00 x 83.00 [1.970 x 1.970 x 3.270]	Configuration Related Features: ? Contact Arrangement = 2 Form C, DPDT, 2 C/O ? Multiple Timing Ranges = Without Industry Standards: ? RoHS/ELV Compliance = Not ELV/RoHS compliant ? Lead Free Solder Processes = Not suitable for lead free processing Conditions for Usage: ? Temperature Range (°C) = -30 – +65 Other: ? Brand = Agastat