molex



Part Number : 2043130010
Product Description : Sentrality 8.00mm Top-entry, Knurled Press-fit Socket Assembly with +/-1.00mm Self-alignment Capability, Tray
Series Number : 204313
Status : Active
Product Category : PCB Headers and Receptacles

Documents and Resources

Drawings

2043130010_sd.pdf

2043650010-PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

2043130001-AS-000.pdf

2043130008-TS-000.pdf

2043131000-TS-000.pdf

2043131234-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

Downloaded from Arrow.com.

EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	204313
Description	Sentrality 8.00mm Top-entry, Knurled Press-fit Socket Assembly with +/-1.00mm Self-alignment Capability, Tray
Application	Busbar-to-Board, Busbar-to-Busbar, Power
Comments	Current and voltage performances are dependent upon application variables.
Component Type	PCB Receptacle
Product Name	Sentrality
UPC	191128468671

Electrical

Current - Maximum per Contact	200.0A
Voltage - Maximum	600V

Downloaded from Arrow.com.

Physical

Breakaway	No
Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	8.00mm
Durability (mating cycles max)	200
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	Yes
Height Above Board	3.40mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Silver
Mating Orientation	Top-entry
Net Weight	11.780/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
PCB Retention	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Press-Fit

Mates With / Use With

Mates with Part(s)

Description	Part Number
Sentrality Pins	203263

Downloaded from Arrow.com.