

## Surge protection device - TTC-6-TVSD-D-48DC-PT-I - 2906852

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fine surge protection with integrated status indicator for a 2-wire floating signal circuit.


The figure shows the version with 24 V DC

### Why buy this product

- ✓ Space-saving installation due to the narrow overall width of 6.2 mm
- ✓ Signaling without additional auxiliary power, thanks to the mechanical status indicator
- ✓ Optional remote signaling module monitors up to 40 items, without additional wiring
- ✓ Quick and tool-free installation of surge protective devices, thanks to Push-in connection technology
- ✓ Safe behavior in the event of overload, thanks to the integrated disconnect device
- ✓ Fine surge protection by means of suppressor diode



### Key Commercial Data

Packing unit	1
GTIN	 4 055626 137087
GTIN	4055626137087
Custom tariff number	85363010

### Technical data

#### Dimensions

Height	92 mm
	92 mm
Width	6.2 mm

# Surge protection device - TTC-6-TVSD-D-48DC-PT-I - 2906852

## Technical data

### Dimensions

Depth	69.5 mm
-------	---------

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Degree of protection	IP20 (with end cover)

### General

Housing material	PBT
Flammability rating according to UL 94	V-0
Color	traffic grey A RAL 7042
Mounting type	DIN rail: 35 mm
Design	Rail-mountable module, one-piece
Direction of action	Line-Earth Ground

### Protective circuit

IEC test classification	C3
Nominal voltage $U_N$	48 V DC
Maximum continuous voltage $U_C$	53 V DC
Rated current	10 A (60°C)
Operating effective current $I_C$ at $U_C$	$\leq 5 \mu A$
Nominal discharge current $I_n$ (8/20) $\mu s$ (core-GND)	90 A
Voltage protection level $U_p$ (core-GND)	$\leq 80 V$ (C3 - 18 A)
Response time $t_A$ (core-earth)	$\leq 1 ns$
Input attenuation $a_E$ , asym.	typ. 0.3 dB ( $\leq 1 MHz / 150 \Omega$ )
Cut-off frequency $f_g$ (3 dB), asym. (GND) in 150 Ohm system	typ. 3.5 MHz
Capacity (Core-GND)	1 nF
Resistance in series	$\leq 100 m\Omega$
Surge protection fault message	optical
Impulse durability (conductor-GND)	C3 - 18 A

### Connection data

Connection method	Push-in connection
Connection method IN	Push-in connection
Connection method OUT	Push-in connection
Stripping length	8 mm
Conductor cross section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross section solid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross section AWG	24 ... 12


Surge protection device - TTC-6-TVSD-D-48DC-PT-I - 2906852

Technical data

Standards and Regulations

Standards/specifications	IEC 61643-21 2000 + corrigendum 2001 + A1:2008, modified + A2:2012
	EN 61643-21 2001 + A1:2009 + A2:2013

Drawings



Approvals

Approvals

Approvals

UL Listed

Ex Approvals

Approval details

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 138168
-----------	---	---	---------------

