

Padlockable Type

• Non-illuminated Emergency Stop Switch

Appearance	NC Main Contact	NO Monitor Contact	Type No.		Operator Color
			IP20 Fingersafe Terminal	w/Terminal Cover	
ø44mm Mushroom  	1NC	—	XN4E-BL401MFRH	XN4E-BL401MRH	Bright red only
	2NC	—	XN4E-BL402MFRH	XN4E-BL402MRH	
	3NC	—	XN4E-BL403MFRH	XN4E-BL403MRH	
	4NC	—	XN4E-BL404MFRH	XN4E-BL404MRH	
	1NC	1NO	XN4E-BL411MFRH	XN4E-BL411MRH	
	2NC	1NO	XN4E-BL412MFRH	XN4E-BL412MRH	
	3NC	1NO	XN4E-BL413MFRH	XN4E-BL413MRH	
	2NC	2NO	XN4E-BL422MFRH	XN4E-BL422MRH	

- Only solid wires can be used on the IP20 fingersafe terminal type.
- Padlocks and hasps are not supplied with the emergency stop switches and must be ordered separately. See page 764.

• Illuminated Emergency Stop Switch

Appearance	Illumination Type	Rated Voltage	NC Main Contact	NO Monitor Contact	Type No.		Operator Color
					IP20 Fingersafe Terminal	w/Terminal Cover	
ø44mm Mushroom  	LED	24V AC/DC	1NC	—	XN4E-LL401Q4MFR	XN4E-LL401Q4MR	Red only
			2NC	—	XN4E-LL402Q4MFR	XN4E-LL402Q4MR	
			3NC	—	XN4E-LL403Q4MFR	XN4E-LL403Q4MR	
			4NC	—	XN4E-LL404Q4MFR	XN4E-LL404Q4MR	
			1NC	1NO	XN4E-LL411Q4MFR	XN4E-LL411Q4MR	
			2NC	1NO	XN4E-LL412Q4MFR	XN4E-LL412Q4MR	
			3NC	1NO	XN4E-LL413Q4MFR	XN4E-LL413Q4MR	
			2NC	2NO	XN4E-LL422Q4MFR	XN4E-LL422Q4MR	

- Only solid wires can be used on the IP20 fingersafe terminal type.
- Padlocks and hasps are not supplied with the emergency stop switches and must be ordered separately. See page 764.

• LED Push-ON Emergency Stop Switch

Appearance	Illumination Type	Rated Voltage	NC Main Contact	NO Monitor Contact	Type No.		Operator Color
					IP20 Fingersafe Terminal	w/Terminal Cover	
ø44mm Mushroom  	LED	24V AC/DC	2NC	—	XN4E-TL402Q4MFR	XN4E-TL402Q4MR	Red only
			3NC	—	XN4E-TL403Q4MFR	XN4E-TL403Q4MR	
			2NC	1NO	XN4E-TL412Q4MFR	XN4E-TL412Q4MR	

- Push-ON type is illuminated when the operator is latched, and turns off when reset.
- Only solid wires can be used on the IP20 fingersafe terminal type.
- Padlocks and hasps are not supplied with the emergency stop switches and must be ordered separately. See page 764.

Flush Silhouette

Control Units

Display Lights

Display Units

Safety Products

Terminal Blocks

Comm. Terminals

AS-Interface

Relays & Timers

Sockets

Circuit Protectors

Power Supplies

PLCs & SmartRelay

Operator Interfaces

Sensors

Control Stations

Explosion Protection

References

XN Series Emergency Stop Switches

XN Series Emergency Stop Switches

XN Series Emergency Stop Switches

XN Series Emergency Stop Switches



XN Series Emergency Stop Switches

XN Series Emergency Stop Switches



XN Series Emergency Stop Switches



XN Series Emergency Stop Switches



XN Series Emergency Stop Switches

XN Series Emergency Stop Switches

XN Series Emergency Stop Switches



XN Series Emergency Stop Switches



XN Series Emergency Stop Switches

XN Series Emergency Stop Switches



XN Series Emergency Stop Switches




XN Series Emergency Stop Switches

Dimensions


Padlockable Type

• Non-illuminated

IP20 Fingersafe




w/Terminal Cover




• Illuminated/Push-ON


IP20 Fingersafe



w/Terminal Cover




Mounting Hole Layout



	X	Y
Plastic Bezel Type	70 mm minimum	
Flush Bezel Type	70 mm minimum	

- The values shown above are the minimum dimensions for mounting with other ø30 mm pushbuttons. For other control units of different sizes and styles, determine the values according to the dimensions, operation, and wiring convenience.
- For padlockable type, determine the values according to the size and number of padlocks and hasp.


LED Unit Internal Circuit




Terminal Arrangement (Bottom View)

Non-illuminated


• NC main contacts only



• With 1NO monitor contact




• With 2NO monitor contacts




Illuminated


• NC main contacts only



• With 1NO monitor contact




• With 2NO monitor contacts





Push-ON

• NC main contacts only




• With 1NO monitor contact




Applicable Crimping Terminal



Ring Terminal



Spade Terminal



Solid Wire



- Be sure to install an insulating tube on the crimping terminal.

All dimensions in mm.