


ITS Series

Illuminated Tactile Switch



Specifications

Function	N.O. Momentary action
Terminals	SMT & Thru-hole
Packaging	Thru-hole: 200 pieces per tray SMT: tape & reel (see V2, V3 or R3N mounting style drawings)

Mechanical Characteristics

Operating Force	160 ± 50gf for V1; V2; V3; R1; R2 models 220 ± 50 gf for R3N model
Operating Life	50,000 cycles (250m Ω max)
Recommended Operating Stroke	0.25mm ± 0.1mm

Electrical Characteristics

Rating	50mA @ 12 VDC
Contact Resistance	< 100 mΩ (initial)
Dielectric Withstanding Voltage	>250VAC (50-60 Hz) between terminals - 1 min.Ω
Insulation Resistance	> 100M Ω
Bounce Time	<10 ms

Environmental Characteristics

Operating Temperature	-25°C to 70°C
Storage Temperature	-25°C to 80°C

Process

Soldering	Thru-hole - wave compatible SMT - convection or IR reflow compatible
------------------	---

Description

The ITS series illuminated tactile switch features vertical and right angle thru-hole and SMT models, ideal for a wide range of products – such as consumer electronics, medical devices and audio/video applications. In addition, multiple custom caps and legends are available to meet application-specific requirements.

Features & Benefits

- Vertical and right angle SMT models
- Vertical and right angle thru-hole models
- Multiple caps and legends
- Several LED colors and bi-color options
- RoHS compliant /compatible

Applications

- Consumer electronics
- Server/storage
- Medical devices
- Test/Measurement/Instrumentation
- Audio/Video
- Computers/Peripherals
- Security

Materials

Contacts/Terminals	Base metal: brass, Plating: Ag
Dome	Base metal: Phosphor bronze plating: Ag
Base	PA
Actuator	PA
Cover	R3N option: Stainless steel V2 & V3 options: PPA Other options: PA
Caps	Caps are ordered separately and shipped bulk. Thru-hole versions available with caps assembled under custom part number. Contact customer service for details.


ITS Series

Illuminated Tactile Switch



Ordering Number

Our easy build-a-switch concept allows you to mix and match options to create the switch you need. To order, select desired option from each category and place it in the appropriate box.



LED Color

00: No light
10: Red
12: Red/Yellow
13: Red/Green
14: Red/Blue
20: Yellow
21: Yellow/Red
23: Yellow/Green
30: Green
31: Green/Red
32: Green/Yellow
40: Blue
41: Blue/Red
50: White
60: True green

Notes:

Other colors available by request

LED Color / Brightness

LED Characteristic	Units	Standard LED Color Options					
		Red (1)	Yellow (2)	Green (3)	Blue (4)	White (5)	True Green (6)
Recommended Operating	mA @ 5VDC	20 mA	20 mA	20 mA	20 mA	20 mA	20 mA
Forward Current	mA	30 mA	30 mA	30 mA	30 mA	30 mA	30 mA
Peak Pulsing Current (1/8 duty @ 1 kHz)	mA	125 mA	125 mA	125 mA	125 mA	125 mA	125 mA
Power Dissipation	mW	75 mW	75 mW	75 mW	75 mW	75 mW	75 mW
Forward Voltage @ 20 mA	Volts	2.5 Volts Max.	2.5 Volts Max.	2.5 Volts Max.	3.6 Volts Max.	3.6 Volts Max.	3.6 Volts Max.
Dominant Wavelength @ 20mA	nm	637nm (Typical)	590nm (Typical)	570nm (Typical)	465nm (Typical)	CIE Coordinates X= 0.25~0.33 Y= 0.24~0.34	522nm (Typical)
Wavelength at Peak Emission @20mA	nm	645nm (Typical)	590nm (Typical)	573nm (Typical)	460nm (Typical)	CIE Coordinates X= 0.25~0.33 Y= 0.24~0.34	515nm (Typical)
Spectral Half Bandwidth @ 20mA	nm	20nm (Typical)	20nm (Typical)	17nm (Typical)	25nm (Typical)	CIE Coordinates X= 0.25~0.33 Y= 0.24~0.34	33nm (Typical)
Luminous Intensity @ 20mA	mcd	50 mcd Min.	125 mcd Min.	40 mcd Min.	100 mcd Min.	250 mcd Min.	500 mcd Min.
Viewing Angle at 50% LV (@ 10mA)	degrees	150° Typical	120° Typical	120° Typical	120° Typical	150° Typical	120° Typical


ITS Series

Illuminated Tactile Switch



Mounting Styles

V1 - Vertical Thru-hole



Note:

Tray packaging: 200 pieces





ITS Series

Illuminated Tactile Switch




V2 - Vertical SMT: Gullwing


Electrical Schematic





P.C.B. Layout



Tape and Reel



Notes:
1. Switch with Temporary Pick and Place Cap.




Note:
Tape and Reel: 500 pieces

ITS Series


Illuminated Tactile Switch



V3 - Vertical SMT: Gull wing with J bend LED



Tape and Reel



Notes:


1. Switch with Temporary Pick and Place Cap.
2. Tape and Reel: 500 pieces

ITS Series

Illuminated Tactile Switch




R1 - Right Angle: Thru-hole



Note:
Tray packaging: 200 pieces

R2 - Right Angle: Thru-hole 2.5mm leads




Note:
Tray packaging: 200 pieces

ITS Series





Illuminated Tactile Switch





R3N - Right Angle, SMT



ELECTRICAL SCHEMATIC



Tape & Reel



Force

Option Code	Force
S	Standard 160 gf - V1, V2, V3, R1, R2 options 220 gf - R3N option

ITS Series

Illuminated Tactile Switch



Caps

399E - A - 0 - 00 - 0

Material:

A: Polycarbonate - Natural/Clear

Paint Color

0: No paint

Marking Color

0: No marking

Marking

00: No Marking


Notes:

Use the individual ordering code for each cap

Note:

All caps not to be used to R3N

399EA0000¹ Round cap, clear



Notes:

1: Not to be used with right angle versions

400E - x - xx - x

Material:

A: Polycarbonate¹ - Natural/Clear

B: Polycarbonate² - Translucent white

C: Polycarbonate - Silver paint laser tech

Paint Color

0: No paint³

A: Matte Silver

Marking Color

0: No marking

E: Laser etch (painted caps only)

Laser Etch

00: No Marking

01: Power On/Off

04: Arrow right

05: Arrow left

06: Arrow up

07: Arrow down

09: Power

33: Arrow up (fill)



Notes:

1: Material A has only one part number 400EA0000

2: Material B has only one part number 400EB0000

3: Paint color option 0 is not available for 400EC

ITS Series



Illuminated Tactile Switch

**400EA0000**

Natural/clear

**400EB0000**

Translucent white, flat edge

**400ECA01E**Matte silver paint
laser etch, flat edge**ITSXXFR1ST & 400ECA01E cap****400ECA01E SHOWN****SECTION A-A**

Notes:
400E cap dimensions shown are "as molded" (no paint).

ITS Series

Illuminated Tactile Switch



401E - x - xx - x

Material:

A: Polycarbonate¹ - Natural/Clear
B: Polycarbonate² - Translucent white
C: Polycarbonate - paint laser tech

Paint Color

0: No paint³
A: Matte Silver

Marking Color

0: No marking
E: Laser etch (painted caps only)


Laser Etch

00: No Marking
06: Arrow up
07: Arrow down
33: Arrow up (fill)
34: Arrow down (fill)


Notes:

- 1:** Material A has only one part number 400EA0000
2: Material B has only one part number 400EB0000
3: Paint color option 0 is not available for 400EC

Dimensions


Notes:

401E cap dimensions shown are "as molded" (no paint).

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.