






10	9	8	7	6	5	4	3	2	1
PART NUMBER	DESCRIPTION		MATERIAL		COLOR				
180560-0001	LED HOLDER - PBT		POLYESTER, GLASS FILLED		WHITE				
180560-0101	LED HOLDER - NYLON		POLYAMIDE, GLASS FILLED		NATURAL				
180560-0002	LED HOLDER w/PRE-HOLD - PBT		POLYESTER, GLASS FILLED		WHITE				
180560-0102	LED HOLDER w/PRE-HOLD - NYLON		POLYAMIDE, GLASS FILLED		NATURAL				








- NOTES:
- 1) MATERIALS: SEE CHART.
 - 2) WIRE TRAP TERMINALS: COPPER ALLOY.
a. FINISH: SELECTIVE GOLD OVER NICKEL.
 - 3) THIS PRODUCT IS ELV AND ROHS COMPLIANT.
 - 4) APPLICABLE WIRE GAUGE - 18 OR 22 AWG
a. SOLID WIRE IS RECOMMENDED.
b. IF STRANDED WIRE IS USED, PRE-TINNED IS RECOMMENDED.
c. 11.0mm±1.0mm STRIP LENGTH IS RECOMMENDED.
 - 5) MOUNT HOLDER USING M2.5 SCREWS (2); 0.40 MIN - 0.80 MAX NEWTON METERS TORQUE.
 - 6) ALL DIMENSIONS IN PARENTHESES "(X.XX)" ARE FOR REFERENCE ONLY.
 - 7) UL:0LFB2 UL496 FILE: E345583.


180560-0001
180560-0101

ENTER DESCRIPTION EC NO: SSL2017-0014 DRAWN: ZABJANOVSKI 2016/10/10 CHKD: CHKD: APPR: GMEYER 2016/10/17 A3	DESCRIPTION 2016/10/17	QUALITY SYMBOLS F_A=0 F_G=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
					DRAWN BY DATE		TITLE COB HOLDER ASSEMBLY 15.85MM X 15.85MM					
					CHECKED BY DATE							
					MCOLE 2013/10/31		molex					
					APPROVED BY DATE							
					DMCGOWAN 2012/08/17							
					MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
					SEE CHART		SD-180560-001		1 OF 2			
					SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										

	10	9	8	7	6	5	4	3	2	1
	COB MFG	TYPE	DIM 'A'	DIM 'B'	THICKNESS	DIM 'C'				
	CREE	CXA1507	15.85	15.85	1.15	10.5				
F	CREE	CXA1510	15.85	15.85	1.15	10.5				
	CREE	CXA1512	15.85	15.85	1.15	10.5				
	CREE	CXA1520	15.85	15.85	1.00	10.5				
	CREE	CXB1507	15.85	15.85	1.15	10.5				
	CREE	CXB1512	15.85	15.85	1.15	10.5				
	CREE	CXB1520	15.85	15.85	1.00	10.5				
E	BRIDGELUX	H9	15.85	15.85	1.10	10.5				








180560-0002
180560-0102



ENTER DESCRIPTION EC NO: SSL2017-0014 DRAWN: ZABJANOVSKI 2016/10/10 CHKD: APPR: GMEYER 2016/10/17	DESCRIPTION	QUALITY SYMBOLS F_A=0 F_G=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY	DATE	TITLE COB HOLDER ASSEMBLY 15.85MM X 15.85MM				
			4 PLACES	± ---	± ---	FJAKLIC	2012/08/10					
			3 PLACES	± ---	± ---	CHECKED BY	DATE	DOCUMENT NO. SD-180560-001				
			2 PLACES	± 0.13	± ---	MCOLE	2013/10/31					
			1 PLACE	± 0.25	± ---	APPROVED BY	DATE	SHEET NO. 2 OF 2				
			0 PLACE	± ---	± ---	DMCGOWAN	2012/08/17					
			ANGULAR ±1/2°		MATERIAL NO.		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART							

10	9	8	7	6	5	4	3	2	1
PART NUMBER	DESCRIPTION		MATERIAL		COLOR				
180560-0001	LED HOLDER - PBT		POLYESTER, GLASS FILLED		WHITE				
180560-0101	LED HOLDER - NYLON		POLYAMIDE, GLASS FILLED		NATURAL				
180560-0002	LED HOLDER w/PRE-HOLD - PBT		POLYESTER, GLASS FILLED		WHITE				
180560-0102	LED HOLDER w/PRE-HOLD - NYLON		POLYAMIDE, GLASS FILLED		NATURAL				








- NOTES:
- 1) MATERIALS: SEE CHART.
 - 2) WIRE TRAP TERMINALS: COPPER ALLOY.
a. FINISH: SELECTIVE GOLD OVER NICKEL.
 - 3) THIS PRODUCT IS ELV AND ROHS COMPLIANT.
 - 4) APPLICABLE WIRE GAUGE - 18 OR 22 AWG
a. SOLID WIRE IS RECOMMENDED.
b. IF STRANDED WIRE IS USED, PRE-TINNED IS RECOMMENDED.
c. 11.0mm±1.0mm STRIP LENGTH IS RECOMMENDED.
 - 5) MOUNT HOLDER USING M2.5 SCREWS (2); 0.40 MIN - 0.80 MAX NEWTON METERS TORQUE.
 - 6) ALL DIMENSIONS IN PARENTHESES "(X.XX)" ARE FOR REFERENCE ONLY.
 - 7) UL:0LFB2 UL496 FILE: E345583.


180560-0001
180560-0101

ENTER DESCRIPTION EC NO: SSL2017-0014 DRAWN: ZABJANOVSKI 2016/10/10 CHKD: APPR: GMEYER 2016/10/17 REV	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION					
		$F_A=0$ $F_G=0$ $F_P=0$		mm	INCH	DRAWN BY	DATE	TITLE COB HOLDER ASSEMBLY 15.85MM X 15.85MM						
			4 PLACES	± ---	± ---	FJAKLIC	2012/08/10							
			3 PLACES	± ---	± ---	CHECKED BY	DATE							
			2 PLACES	± 0.13	± ---	MCOLE	2013/10/31							
			1 PLACE	± 0.25	± ---	APPROVED BY	DATE							
		0 PLACE	± ---	± ---	DMCGOWAN	2012/08/17	molex							
		ANGULAR ±1/2°		MATERIAL NO.		DOCUMENT NO.						SHEET NO.		
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-180560-001						1 OF 2		
				SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									

	10	9	8	7	6	5	4	3	2	1
	COB MFG	TYPE	DIM 'A'	DIM 'B'	THICKNESS	DIM 'C'				
	CREE	CXA1507	15.85	15.85	1.15	10.5				
F	CREE	CXA1510	15.85	15.85	1.15	10.5				
	CREE	CXA1512	15.85	15.85	1.15	10.5				
	CREE	CXA1520	15.85	15.85	1.00	10.5				
	CREE	CXB1507	15.85	15.85	1.15	10.5				
	CREE	CXB1512	15.85	15.85	1.15	10.5				
	CREE	CXB1520	15.85	15.85	1.00	10.5				
E	BRIDGELUX	H9	15.85	15.85	1.10	10.5				



180560-0002
180560-0102



ENTER DESCRIPTION EC NO: SSL2017-0014 DRAWN: ZABJANOVSKI 2016/10/10 CHKD: APPR: GMEYER 2016/10/17 A3	DESCRIPTION 2016/10/17	QUALITY SYMBOLS F _A =0 F _G =0 F _P =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION				
				mm	INCH	DRAWN BY FJAKLIC	DATE 2012/08/10	TITLE COB HOLDER ASSEMBLY 15.85MM X 15.85MM					
			4 PLACES	± ---	± ---	CHECKED BY	DATE						
			3 PLACES	± ---	± ---	MCOLE	2013/10/31	molex					
			2 PLACES	± 0.13	± ---	APPROVED BY	DATE						
			1 PLACE	± 0.25	± ---	DMCGOWAN	2012/08/17						
			0 PLACE	± ---	± ---	MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
			ANGULAR ±1/2°		SEE CHART		SD-180560-001				2 OF 2		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							